





REVISION RECORD		
REV	DESCRIPTION	DRFT
11	EXTEND MIDDLE METAL SPACER (DIM0.15) CONTROL METAL SPACER POSITION (DIM1.5)	Royzuo 6/06/13




- NOTES:
- MATERIAL:
CONNECTOR
HOUSING: GLASS FILLED LCP, UL94 V-0, BLACK
TERMINALS: PHOS-BRONZE t=0.2mm .
OVERMOLDED TERMINALS HOUSING: GLASS FILLED LCP, UL94 V-0, BLACK
CAGE ASSEMBLY: COPPER-NICKEL-ZINC ALLOY t=0.25mm.
LIGHT PIPES: POLYCARBONITE UL94V-0, CLEAR.
 - FINISH:
TERMINAL:
1)50u" MIN NICKEL PLATING OVER ALL.
2)COMPLIANT TAIL: 50u" TIN OVER 50u" MIN NICKEL.
3)30u" MIN GOLD PLATING ON MATING AREA.
 - PRESS FIT HOLES:
CONTACT:
1)HOLE DIAMETER AFTER PLATING: 0.41-0.51mm.
2)DRILLED HOLE: 0.535-0.585mm
CAGE:
1)HOLE DIAMETER AFTER PLATING: 1.00-1.10mm.
2)DRILLED HOLE: 1.125-1.175mm.
 - RATING:
1)VOLTAGE: 120V r.m.s
2)CURRENT RATING: 0.5Amp. MAXIMUM PER INDIVIDUAL CONTACT.
3)OPERATING TEMPERATURE: -55°C TO 85°C
4)INSULATION RESISTANCE: 1000 mega-ohms Min.


Qty Per:	TRAY	CARTON
	3	18



DETACHED LISTS	<div><div>MM</div><div>(INCH)</div></div>		RoHS Compliant		<div><div></div><div>Pulse Electronics</div></div>			
	TOLERANCES EXCEPT AS NOTED		TITLE					
	MM		METAL GASKET					
	.0 ± 0.25	±	SFP PLUS 2 BY 4 CAGE+CONNECTOR_P					
	.00 ± 0.20	±						
	.000 ± 0.10	±						
	ANGLES ± 1°		DFTO : JACK		DRAWING NO. CSFPP014-L		SIZE	REV
			DATE : 10/15/10		/PART NO. SFPP014-L		A3	11
	THIRD ANGLE PROJECTION		SCALE : 1:1		DO NOT SCALE DRAWING		SHEET	1 OF 4

REVISION RECORD		
REV	DESCRIPTION	DRFT
11	EXTEND MIDDLE METAL SPACER (DIM0.15) CONTROL METAL SPACER POSITION (DIM1.5)	Royzuo 6/05/13'








BEZEL CUT-OUT CENTER SPACING DETAIL
BEZEL THICKNESS:0.8–2.6




DETACHED LISTS	<div><div>MM</div><div>(INCH)</div></div>		RoHS Compliant		<div><div></div><div>Pulse Electronics</div></div>		
	TOLERANCES EXCEPT AS NOTED		TITLE				
	MM		METAL GASKET				
	.0 ± 0.25	±	SFP PLUS 2 BY 4 CAGE+CONNECTOR_P				
	.00 ± 0.20	±					
	.000 ± 0.10	±					
	ANGLES ± 1°		DFTO : JACK	DRAWING NO. CSFPP014-L		SIZE	REV
			DATE : 10/15/10	/PART NO. SFPP014-L		A3	11
	THIRD ANGLE PROJECTION		SCALE : 1:1	DO NOT SCALE DRAWING		SHEET	2 OF 4

REVISION RECORD		
REV	DESCRIPTION	DRFT
11	EXTEND MIDDLE METAL SPACER (DIM0.15) CONTROL METAL SPACER POSITION (DIM1.5)	Royzuo 6/05/13'




DETACHED LISTS	<div><div>MM</div><div>(INCH)</div></div>		RoHS Compliant		<div><div></div><div>Pulse Electronics</div></div>		
	TOLERANCES EXCEPT AS NOTED		TITLE				
	MM		METAL GASKET				
	.0 ± 0.25	±	SFP PLUS 2 BY 4 CAGE+CONNECTOR_P				
	.00 ± 0.20	±					
	.000 ± 0.10	±					
	ANGLES ± 1°		DFTO :	JACK	DRAWING NO.	CSFP014-L	SIZE
<div><div></div><div></div></div>		DATE :	10/15/10	/PART NO.	SFP014-L	A3	11
THIRD ANGLE PROJECTION		SCALE :	1:1	DO NOT SCALE DRAWING		SHEET	3 OF 4


REVISION RECORD		
REV	DESCRIPTION	DRFT
11	EXTEND MIDDLE METAL SPACER (DIM0.15) CONTROL METAL SPACER POSITION (DIM1.5)	Royzuo 6/05/13'



KEEP-OUT ZONE DETAIL
SCALE 6:1



CONNECTOR PIN-OUT
COMPONENT SIDE OF BOARD



DETAIL A
SCALE 6:1

NOTES: LED PROFILE (0603)
HEIGHT:0.6mm~0.8mm
VIEW ANGLE:≤120°

DETACHED LISTS	<div><div>MM</div><div>(INCH)</div></div>		RoHS Compliant		<div><div><div></div></div><div>Pulse</div><div>Electronics</div></div>			
	TOLERANCES EXCEPT AS NOTED							
	MM		TITLE				METAL GASKET	
	.0 ± 0.25	±	SFP PLUS 2 BY 4 CAGE+CONNECTOR_P					
	.00 ± 0.20	±						
	.000 ± 0.10	±						
	ANGLES ± 1°		DFTO : JACK		DRAWING NO. CSFPP014-L		SIZE	REV
			DATE : 10/15/10		/PART NO. SFPP014-L		A3	11
	THIRD ANGLE PROJECTION		SCALE : 1:1		DO NOT SCALE DRAWING		SHEET	4 OF 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

SFPP014-L