




REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD
1		MODIFY DIM	ANKUE	
			9/13/05	



PC Board Layout Component Side Shown

NOTES:**ELECTRICAL:**

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 45MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL : PHOSPHOR BRONZE t=0.35mm.
3. PLATING : GOLD PLATING OVER NICKEL.
4. OPERATING LIFE : 750 CYCLES MIN.
5. PCB RETENTION PRE-SOLDER : 1 LB MIN.
6. PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO +85°C.
2. OPERATION: 0°C TO 70°C.
3. WAVE SOLDER TEMPERATURE: 230°C TO 250°C 3~5 SECOND.

MATES WITH MODULAR PLUG CONFORMING TO

FCC PART 68, SUBPART F.

CUL FILE NO. E163191

PART NUMBER: E560X-XS008X-L

- 8-8C 1-10C
- 1- 3U" 2- 6U"
- 3- 15U" 4- 30U"
- 5- 50U"
- 2- W/O LOGO TIN
- 3- W/O LOGO NICKEL

DETACHED LISTS	MM (INCH)	DFTO ANKUE	DATE 5/27/2005	FULL RISE ELECTRONIC CO., LTD	
	TOLERANCES EXCEPT AS NOTED	CHKD JAKE	DATE 2005/09/14		
	MM	MFO	DATE	TITLE	
	.0 ±0.20	APPVLLUSHENG	DATE 2005/09/14	11.5 SIDE ENTRY PCB JACK 8P (W/TABS)	
	.00 ±0.15			DRAWING NO. GE563116-LC	
	.000 ±0.075			/PART NO. SEE NOTE	
	ANGLES ±			SIZE A3	
	THIRD ANGLE PROJECTION			REV 1	
				DO NOT SCALE DRAWING	
				SHEET X OF Y	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5608-3S0084-L](#)