


THT Common Mode Chokes

PMC9539.XXXNL Series



- EP16 Platform
- Round Wire Coil
- 19.6x17.8x15.5mm
- 90uH/25A to 250uH/18A
- 1000Vdc Isolation

Electrical Specifications @ 25°C - Operating Temperature -40°C to +125°C

Part Number	Inductance (1-2)=(3-4)	I _{rated}	Leakage Inductance (1-2) with (3-4) shorted	Capacitance (1,2) to (3,4)	DCR (1-2)=(3-4)	Self Resonant Frequency (1-2)=(3-4)	Impedance @ SRF
	(uH MIN/TYP)	(A)	(uH TYP/MAX)	(pF TYP/MAX)	(mΩ MAX)	(MHz TYP)	(Ω TYP)
PMC9539.903NL	58/90	25	0.8/1.5	10/20	1.3	2.1	250
PMC9539.164NL	100/160	22	1.0/2.0	13/26	1.7	1.9	450
PMC9539.254NL	160/250	18	1.3/2.6	16/30	2.7	1.6	750




NOTE:

- The current rating (I_{rated}) is based upon the temperature rise of the component and represents the rms current which will cause a typical temperature rise of 50°C with free air cooling.
- The temperature of the component (ambient plus temperature rise) must be within the stated operating temperature range.



Mechanicals

Schematic


PMC9539.XXXNL



FINAL OUTLINE



SUGGESTED LAND PATTERN



Weight (TYP)18 grams

Tray150/ Tray

Dimensions: mm

Unless otherwise specified, all tolerance are ±0.25


Part Number	A Dimension	B Dimension
PMC9539.903NL	1.45±0.1	1.85
PMC9539.164NL	1.45±0.1	1.85
PMC9539.254NL	1.25±0.1	1.65

THT Common Mode Chokes

PMC9539.XXXNL Series

Impedance Plots

PMC9539 Impedance Vs Frequency



For More Information:

Americas - prodinfo_power_americas@pulseelectronics.com | Europe - prodinfo_power_emea@pulseelectronics.com | Asia - prodinfo_power_asia@pulseelectronics.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2022. Pulse Electronics, Inc. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[PMC9539.164NL](#) [PMC9539.254NL](#) [PMC9539.903NL](#)