


REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD

**NOTES:****ELECTRICAL:**

1. VOLTAGE RATING: 125 VAC RMS .
2. CURRENT RATING: 1.5 AMP .
3. CONTACT RESISTANCE: 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH: 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

1. HOUSING MATERIAL: GLASS FILLED POLYESTER UL 94V-0
2. CONTACT MATERIAL: PHOSPHOR BRONZE. t=0.35mm
3. PLATING: GOLD PLATING OVER NICKEL.
4. OPERATING LIFE: 750 CYCLES MIN.
5. PCB RETENTION PRE-SOLDER: 1 LB MIN.
6. PCB RETENTION POST-SOLDER: 10 LBS MIN.


ENVIRONMENTAL:

1. STORAGE: -40°C TO +85°C.
2. OPERATION: -40°C TO +85°C.
3. WAVE SOLDERING TEMPERATURE: 230°C TO 250°C (3-5SECOND).


PART NUMBER: E526X-70004X-L

2- 2CONTACTS
4- 4CONTACTS
6- 6CONTACTS

1- 3u" 2- 6u" 3-15u"
4-30u" 5-50u"



RECOMMENDED HOLE PATTERN
(COMPONENT SIDE VIEW)

DETACHED LISTS	<div>MM (INCH)</div>		DFTO SAMMYWEN		DATE 05/27/05		FULL RISE ELECTRONIC CO., LTD			
	TOLERANCES EXCEPT AS NOTED		CHKD ANKUE		DATE 2005/5/28					
			MFO		DATE		TITLE			
			APPV LUSHENG		DATE 2005/5/28					
			MATERIAL :		TOP ENTRY PCB JACK (DIP TYPE)					
	ANGLES ±		QT'Y :							
	<div></div>		FINISH :		DRAWING NO. GE523030-LC				SIZE	REV
	THIRD ANGLE PROJECTION		SCALE :		/PART NO. SEE NOTE				A3	0
					DO NOT SCALE DRAWING				SHEET X	OF Y

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5262-700045-L](#)