


Electrical




SCHEMATIC

ELECTRICAL SPECIFICATIONS @ 25°C

URNS RATIO	: 1 : 1 ± 5%
PHASING	: 1, 4 AND 7 – 10, 13 AND 16
OCL	: 67 μ H – 110 μ H @ 5mV, 10KHz
LL	: 0.25 μ H MAX @ 1MHz MIN
C _{ww}	: 10pF MAX @ 140KHz
ET	: 2.4V– μ SEC MIN
DCR	: 0.30 Ω MAX
HI POT	: 500VRMS (WINDING – WINDING)
RISE TIME	: 3nS MAX

Mechanical



	MILLIMETERS		INCHES	
DIM	MIN	MAX	MIN	MAX
A	19.89	20.39	.783	.803
B	6.60	7.11	.260	.280
C	4.62	5.13	.182	.202
D	17.78 (TP)		.700 (TP)	
E	7.24	8.00	.285	.315
F	.38	.89	.015	.035
G	2.54 (TP)		.100 (TP)	
(H)	8.89	9.65	.350	.380
J	.38	.53	.015	.021
K	.18	.33	.007	.013
L	3.18	3.81	.125	.150
(P)	.66	1.68	.026	.066

WEBSITE www.valorinc.com E-MAIL marketing@valorinc.com

NORTH AMERICA
tel 1-800-31 VALOR
fax 619-537-2525

ASIA/PACIFIC
tel +852-2953-1000
fax +852-2953-1333

EUROPE
tel +44-1727-824 875
fax +44-1727-824 898

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

LT6002