








	REVISION DESCRIPTION	APP.	DRW.	DATE	CHANGE No.
△ x 1	Change the note	H.T.	O.S.	11/24/25	DC15-0051
△ x					
△ x					



SPECIFICATIONS

MATERIALS AND FINISHES:
 INSULATOR: THERMOPLASTIC, UL94 V-0.
 CONTACTS: COPPER ALLOY.
 FUNCTION AREA PLATING: Au 15u" OVER Ni; TAIL AREA PLATING: Sn OVER Ni.
MECHANICAL:
 DURABILITY: 250 CYCLES
 INSERTION/EXTRACTON FORCE: 40N MAX. / 11.5N MAX.
PHYSICAL:
 OPERATING TEMPERATURE: -55°C TO +85°C
ELECTRICAL:
 CONTACT RESISTANCE: 20m Ohms MAX.
 VOLTAGE RATING: 30V AC RMS MAX.
 INSULATION RESISTANCE: 1000M Ohms Min.
 CURRENT RATING: 0.5 A MAX.
 RoHS DIRECTIVE COMPLIANCE<LEAD-FREE> REFLOW CAPABLE TO 260±10°C,10SEC

General Tolerances (Unless Specified)	
	mm
4 Place	±0.10
3 Place	±0.10
2 Place	±0.20
1 Place	±0.30
Angular	±1°

SFP+ CONNECTOR,20P,SMT,Au,15u"								YAMAICHI ELECTRONICS USA INC.	
								CLASS	
SCALE	5/1	APP.	APP.	CHK.	DRW.	DSGN.	TITLE		
DATE	08/15/2011	08/15/2011	08/15/2011	08/15/2011	08/15/2011	08/15/2011	CNU109S-020-0010		
DRW No.	YEU-A1711	1/1	REV.		B				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Yamaichi Electronics:](#)

[CNU109S-020-0010](#)