



Schematic



Dimensions (in.)

■ SPECIFICATIONS

- Frequency: 796kHz
- Inductance 1-3: $360\mu\text{H}$ @ 455kHz
- Unloaded Q 1-3: 80 min.
- Turns: 1-2: 104, 2-3: 3, 1-3: 107, 4-6: 8
- Dielectric strength: 100VDC for 1 minute
- Insulating resistance: $100\text{M}\Omega$ @ 100VDC
- RoHS Compliant

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[42IF100-RC](#)