

Industrial Class Power Supplies

Industrial Mini-Redundant AC Power Supply



Model Name	Power (typical)	Maximum DC Output Current						Current Type	AC Voltage Input Range	Certifications
		+5 V	+3.3 V	+12 V	-12 V	-5 V	+5 Vsb			
APS-930XAR	300 W	25 A	18 A	16 A	0.5 A	0.5 A	2.0 A	ATX12V	110 ~ 220 VAC (±10%)	UL/CSA/TUV
APS-946XAR	460 W	25 A	25 A	30 A	0.8 A	--	2.0 A	EPS12V	110 ~ 220 VAC (±10%)	UL/CSA/TUV

■ Dimensions: 185 x 150 x 86 (mm)

Industrial Dual Redundant AC Power Supply



Model Name	Power (typical)	Maximum DC Output Current						Current Type	AC Voltage Input Range	Certifications
		+5 V	+3.3 V	+12 V	-12 V	-5 V	+5 Vsb			
APS-6300F	300 W + 300 W	36 A	25 A	17 A	0.8 A	0.8 A	1 A	ATX/ ATX12V	Manual switch 100 ~ 120 VAC (±10%) 200 ~ 220 VAC (±10%)	UL/CSA/TUV
APS-6400F	400 W + 400 W	36 A	25 A	17 A	0.8 A	0.8 A	1 A	ATX/ ATX12V	Manual switch 100 ~ 120 VAC (±10%) 200 ~ 220 VAC (±10%)	UL/CSA/TUV

■ Dimensions: 187 x 167 x 183 (mm) ■ Non RoHS

Industrial AC Power Supply PS2 Form Factor



Model Name	Power (typical)	Maximum DC Output Current						Current Type	AC Voltage Input Range	Certifications
		+5 V	+3.3 V	+12 V	-12 V	-5 V	+5 Vsb			
APS-935XA-EPS12	350 W	35 A	28 A	26 A	0.8 A	0.5 A	2 A	EPS12V	110 ~ 220 VAC (±10%)	UL/CSA/TUV
APS-940XA-ATX12	400 W	35 A	28 A	30 A	0.8 A	0.5 A	2 A	ATX12V	110 ~ 220 VAC (±10%)	UL/CSA/TUV
APS-940XA-EPS12	400 W	35 A	28 A	30 A	0.8 A	0.5 A	2 A	EPS12V	110 ~ 220 VAC (±10%)	UL/CSA/TUV
APS-946XA-EPS12	460 W	40 A	30 A	32 A	1 A	0.8 A	2 A	EPS12V	110 ~ 220 VAC (±10%)	UL/CSA/TUV

■ Dimensions: Standard PS2 form factor, 140 x 150 x 86 (mm)

Industrial DC-DC Power Supply PS2 Form Factor



Model Name	Power (typical)	Maximum DC Output Current						Current Type	DC Voltage Input Range	Certifications
		+5 V	+3.3	+12 V	-12 V	-5 V	+5 Vsb			
APS-930/48X	300 W	35 A	30 A	8 A	1 A	0.5 A	1.5 A	ATX	40 ~ 72 VDC (48 VDC nominal)	UL/CUL/TUV

■ Dimensions: 150 x 140 x 86 (mm)

Industrial AC Power Supply 1U Form Factor



Model Name	Power (typical)	Maximum DC Output Current						Current Type	AC Voltage Input Range	Certifications
		+5 V	+3.3 V	+12 V	-12 V	-5 V	+5 Vsb			
APS-9125XU	250 W	25 A	14 A	12 A	1 A	0.5 A	1.5 A	ATX12V	110 ~ 220 VAC (±10%)	UL/CSA/TUV
APS-9130XU	300 W	24 A	20 A	20 A	0.5 A	0.5 A	1.5 A	ATX12V	110 ~ 220 VAC (±10%)	UL/CSA/TUV

■ Dimensions: 205 x 100 x 40.5 (mm)

Industrial Flex ATX AC Power Supply for 1U Chassis



Model Name	Power (typical)	Maximum DC Output Current						Current Type	AC Voltage Input Range	Certifications
		+5	+3.3 V	+12 V	-12 V	-5 V	+5 Vsb			
APS-918XU	180 W	16 A	14 A	14 A	0.5 A	--	2 A	ATX	110 ~ 220 VAC (±10%)	UL/CUL/TUV

■ Dimension: 150 x 81.5 x 40.6 (mm)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[APS-9130XU, 300W, 1U](#)