

GM-270SG

27" LED-framed
Gaming Monitor



Features

- 27" 16:9 LCD panel with LED backlight with 50,000-hour service life
- Display with surrounding LED (addressable RGB LEDs)
- Anti-fingerprint surface treatment for ease of cleaning and enhanced readability
- Wide viewing angles support for both portrait and landscape modes

Ordering Information

- GM-270SG
27" LED-framed Gaming Monitor

Optional Accessories

- AC Adapter
- LED Control Board

GM-270SG			
Display		Environmental	
Size	27"	Operating Temperature	0°C to 50°C
Resolution	1920 x 1080	Storage Temperature	-20°C to 60°C
Aspect Ratio	16:9	Humidity	10% to 80% @ 40°C (non-condensing)
Color	16.7M	Surface Hardness	7H
Brightness (Nits)	450 nits	Vibration	Operating: 1G random 5 to 500Hz
Backlight Life (Hrs)	50,000	Shock	Operating: 20G acceleration part to part, 11ms
Viewing Angle (U/D/R/L)	89/89/89/89	Certifications & Compliance	CE/FCC
Contrast Ratio	1000:1	Power Input	DC-12V 5A Max.
Surface Treatment	Anti-fingerprint coating	Power Consumption	25W
Bonding	Air bonding	LED Strip Power	5V DC, 2.2A Max.
I/O		Mechanical	
Video	DPx1, DVIx1, VGAx1	Weight	9 kg
Audio	w/o Audio	Dimensions (H x W x D)	660 x 404x 50 mm
		Mounting	VESA Mount, M4 MIS-D 75mm x 75mm, 100mm x 100mm (Standard)

All products and company names listed are trademarks or trade names of their respective companies. Updated Jul. 27, 2023. ©2023 ADLINK Technology, Inc. All Rights Reserved. All pricing and specifications are subject to change without further notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[GM-270G](#) [GM-270SG](#)