



lumbergautomation

A **BELDEN** BRAND



Profibus Signal Cables

0975 254 131



0975 254 131/...M

Single-ended Profibus signal cable, M12 female right angle connector B coded, molded on one side, 360° shielding connected to knurled nut.

0975 254 132



0975 254 132/...M

Single-ended Profibus signal cable, M12 male right angle connector B coded, molded on one side, 360° shielding connected to knurled nut.

0975 254 130



0975 254 130/...M

Double-ended cord set, 360° shielding, M12 male right angle connector to M12 female right angle connector, 5 poles, B-coding.

0975 254 134




0975 254 134/...M

Double-ended cord set, 360° shielding, M12 male right angle connector to M12 female straight connector, 5 poles, B-coding.

Pin Assignment

M12 male/female connector, 5 poles



Part Number	Standard Cable Lengths	
0975 254 130/...M	0.3 M 0.6 M 1 M 2 M 3 M 5 M 10 M	UL    
0975 254 131/...M	2 M 5 M 10 M	UL    
0975 254 132/...M	2 M 5 M 10 M	UL    
0975 254 134/...M	1 M 2 M 3 M	UL    

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

[0975 254 130/1 M](#) [0975 254 132/2 M](#) [0975 254 130/3 M](#) [0975 254 130/0,3 M](#) [0975 254 130/10 M](#) [0975 254 130/5 M](#)
[0975 254 132/5 M](#) [0975 254 134/2 M](#) [0975 254 134/3 M](#) [0975 254 134/1 M](#) [0975 254 131/5 M](#) [0975 254 132/10 M](#)
[0975 254 130/2 M](#) [0975 254 131/10 M](#) [0975 254 130/0,6 M](#) [0975 254 131/2 M](#)