



Product: [1213A](#)

Instrument Medical Interconnect, #26-8c, TC, PVC, O/A Foil, PVC Jkt, CL2X

Product Description

Computer, Instrument & Medical Interconnect, 26 AWG stranded (7x34) tinned copper conductors, PVC insulation, Duofoil® shield (100% coverage), 26 AWG stranded tinned copper drain wire, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	for use with Molex SEMMCONN/AMP SDL connectors; computer communications; medical electronics interconnects; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; panel wiring
------------------------	---

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Conductor(s)	8	26	7x34	TC - Tinned Copper

Insulation			
Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.048 in (1.2 mm)	Black, Purple, Red, Blue, Green, Orange, Yellow, White

Outer Shield			
Shield Type	Material	Coverage	Drainwire Type
Tape	Tri-Laminate (Alum+Poly+Alum)	100%	26 AWG (7x34) TC

Outer Jacket		
Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.0385 in (0.978 mm)	0.239 in (6.07 mm)

Electrical Characteristics

Electricals			
Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Velocity of Prop.	Max. Current
44.4 Ohm/1000ft	26 pF/ft (85 pF/m)	60%	1.12 Amps per Conductor at 25°C

Voltage	
UL Voltage Rating	
300 V	

Mechanical Characteristics

Temperature	
UL Temperature	Operating
90°C	-20°C To +90°C

Bend Radius	
Stationary Min.	Installation Min.
2.39 in (60.7 mm)	2.39 in (60.7 mm)

Max. Pull Tension:	28.8 lbs (13.1 kg)
Bulk Cable Weight:	21 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Sunlight Resistance, Burial
Flammability / Reaction to Fire:	VW-1
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, CL2X
AWM Compliance:	AWM 2464
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

Product Notes

Notes:	AMP is a registered trademark of AMP, Inc.
--------	--

History

Update and Revision:	Revision Number: 0.503 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
1213A 010500	Black	Reel	500 ft	612825108672
1213A 0101000	Black	Reel	1,000 ft	612825108665

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1213A 010500](#) [1213A 0101000](#)