



Product: [1508A](#)



Audio Cable, #24-2c, TC, O/A Foil, CM

Product Description

Audio Cable, CM-Rated, 1-24 AWG stranded tinned copper pair with polyolefin insulation, Beldfoil® shield, drain, PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	for use with automatic stripping equipments; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	--

Construction Details

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	24 AWG	7x32	TC - Tinned Copper

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PP - Polypropylene	0.008 in (0.20 mm)	0.04 in mm	Black & Red

Shield Type	Material	Coverage	Drainwire Type
Tape	Tri-Laminate (Alum+Poly+PVC)	100%	24 AWG (7x32) TC

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.024 in (0.61 mm)	0.131 in
Overall Cable Diameter (Nominal):		0.131 in

Electrical Characteristics

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Velocity of Prop.	Max. Current
28.3 Ohm/1000ft	31 pF/ft (100 pF/m)	58 pF/ft (190 pF/m)	66%	3.3 Amps per Conductor at 25°C

UL Voltage Rating
300 V

Mechanical Characteristics

UL Temperature	Operating
60°C	-20°C To +60°C

Stationary Min.	Installation Min.
1.31 in (33.3 mm)	1.31 in

Max. Pull Tension:	16.5 lbs (7.48 kg)
Bulk Cable Weight:	11 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	UL 1685 UL Loading, UL 1685 Vertical Tray, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CM
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Jacket and shield are bonded so both can be removed with automatic stripping equipment.
--------	---

History

Update and Revision:	Revision Number: 0.447 Revision Date: 02-15-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1508A B59500	Black, Matte	Reel	500 ft	612825116721	
1508A B591000	Black, Matte	Reel	1,000 ft	612825116714	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1508A B591000](#) [1508A B59500](#)