



Product: [5000UP](#)

Audio Cable, 2 Conductor 12 AWG, BC, Unshielded, CL3

Product Description

Audio Cable, Rated-CL3, 2-12 AWG highly flexible stranded bare copper conductors with PVC insulation, PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	12 AWG	65x30	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.023 in (0.58 mm)	0.138 in (3.51 mm)	Black, White

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.018 in (0.46 mm)	0.312 in (7.92 mm)	Yes

Overall Cable Diameter (Nominal):	0.312 in (7.92 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	1.56 Ohm/1000ft	32 pF/ft (100 pF/m)	30 Amps per conductor @ 30°C

Voltage

UL Voltage Rating
300 V (CL3)

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
3.1 in (79 mm)	3.1 in (79 mm)

Max. Pull Tension:	169 lbs (76.7 kg)
Bulk Cable Weight:	59 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	UL 1685 UL loading , FT4, IEEE 1202 FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, CL3
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.490 Revision Date: 02-15-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
5000UP 010500	Black	Reel	500 ft	612825436508	
5000UP 010U500	Black	UnReel	500 ft	612825433460	
5000UP 0101000	Black	Reel	1,000 ft	612825154754	C
5000UP D15500	Blue	Reel	500 ft	612825336327	C
5000UP D151000	Blue	Reel	1,000 ft	612825154679	
5000UP 008500	Gray	Reel	500 ft	612825154723	C
5000UP 0081000	Gray	Reel	1,000 ft	612825154693	
5000UP 0051000	Green, Dark	Reel	1,000 ft	612825154686	C
5000UP 009U500	White	UnReel	500 ft	612825154747	
5000UP 0091000	White	Reel	1,000 ft	612825154716	

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[5000UP 010500](#) [5000UP 0091000](#) [5000UP 0101000](#) [5000UP 008500](#) [5000UP 0051000](#) [5000UP 0081000](#)
[5000UP D151000](#) [5000UP D15500](#)