



**Product:** [5100FE](#)

Security & Sound, 2 Conductor 14 AWG, BC, Shielded, CL3R, FPLR

Product Description

Security & Commercial Audio Cable, Riser-CL3R-FPLR, 2-14 AWG stranded bare copper conductors with polypropylene insulation, Beldfoil® shield and PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Intercom/PA Systems, Sound/Audio Systems, Fire Alarm Systems
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	14 AWG	19x26	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PP - Polypropylene	0.011 in (0.28 mm)	0.092 in (2.3 mm)	Black, White

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.222 in (5.64 mm)	Yes

Overall Cable Diameter (Nominal):	0.222 in (5.64 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	2.54 Ohm/1000ft	54 pF/ft (180 pF/m)	97.25 pF/ft (319.1 pF/m)	25 Amps per conductor @ 30°C

Voltage

UL Voltage Rating
300 V (CL3R, FPLR)

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
2.2 in (56 mm)	2.2 in (56 mm)

Max. Pull Tension:	104.1 lbs (47.22 kg)
Bulk Cable Weight:	37 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL 1666 Riser, IEEE 1202 FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 760, CL3R, FPLR
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6100FH

History

Update and Revision:	Revision Number: 0.529 Revision Date: 02-15-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
5100FE.00152	Chrome	Reel	152 m	8719605007704	
5100FE.00305	Chrome	Reel	305 m	8719605007728	
5100FE.001000	Chrome	Reel	1,000 m	8719605007698	
5100FE 008500	Gray	Reel	500 ft	612825156222	
5100FE 0081000	Gray	Reel	1,000 ft	612825156246	C
5100FE 008U1000	Gray	UnReel	1,000 ft	612825423591	
5100FE 008Z1000	Gray	ReelTuff Box	1,000 ft	612825156260	
5100FE.003000	Gray	Reel	3,000 m	8719605007711	
5100FE 0021000	Red	Reel	1,000 ft	612825423584	C
5100FE 002Z1000	Red	ReelTuff Box	1,000 ft	612825156239	

© 2024 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[5100FE 008U1000](#) [5100FE 0021000](#) [5100FE 008500](#) [5100FE 0081000](#)