


Product: [5300UP](#) 

Audio Cable, 2 Conductor 18 AWG, BC, Unshielded, CM



Product Description

Commercial Audio Cable, Rated-CM, 2-18 AWG highly flexible stranded bare copper conductors with PVC insulation, PVC jacket with ripcord

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
18	42x34	BC - Bare Copper	2

Conductor Count: 2

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.015 in

Color Chart

Number	Color
1	Black
2	White

Outer Shield Material

Material
No Shield

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.184 in	0.015 in	Yes

Construction and Dimensions

Cabling

Twists
5.3 twist/ft

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
6.27 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
27 pF/ft

Inductance

Nominal Inductance

0.17 μH/ft

Current

Max. Recommended Current [A]
12.2 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	18 lbs/1000ft
Max. Pull Tension:	42 lbs
Min Bend Radius/Minor Axis:	1.75 in

Standards

NEC/(UL) Compliance:	CM
----------------------	----

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
5300UP 0101000	Black	Reel	1,000 ft	612825421573
5300UP 010Z1000	Black	ReelTuff Box	1,000 ft	612825159322
5300UP D15500	Blue	Reel	500 ft	612825159315
5300UP D151000	Blue	Reel	1,000 ft	612825159339
5300UP D15U1000	Blue	UnReel	1,000 ft	612825336822
5300UP 0081000	Gray	Reel	1,000 ft	612825421566
5300UP 008Z1000	Gray	ReelTuff Box	1,000 ft	612825159391
5300UP 005U500	Green, Dark	UnReel	500 ft	612825159377
5300UP 0051000	Green, Dark	Reel	1,000 ft	612825159346
5300UP 005U1000	Green, Dark	UnReel	1,000 ft	612825159353
5300UP 009500	White	Reel	500 ft	612825159384
5300UP 009U1000	White	UnReel	1,000 ft	612825159407

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.260 Revision Date: 06-24-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[5300UP 0081000](#) [5300UP D151000](#) [5300UP D15500](#) [5300UP 0101000](#) [5300UP 0051000](#) [5300UP 009500](#)