




Product: [5302UE](#) 

Security & Sound, #18-4c, BC, CMR

Product Description

Security & Sound Cable, Riser-CMR, 4-18 AWG stranded bare copper conductors with polyolefin insulation, PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
18	7x26	BC - Bare Copper	4

Conductor Count:	4
------------------	---

Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.008 in

Color Chart

Color
Black
Red
White
Green

Outer Shield Material

Material
No Shield

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.184 in	0.017 in	Yes

Construction and Dimensions

Cabling

Lay Direction	Twists
Left Hand	3 twist/ft

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
6.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
22 pF/ft

Current

Element	Max. Recommended Current [A]
10C Temperature Rise	4 Amps per Conductor at 25°C (10°C Temperature Rise)

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	28 lbs/1000ft
Max. Pull Tension:	90 lbs
Min Bend Radius/Minor Axis:	1.8 in

Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1666 Riser
IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6302UE

Part Number

Variants

Item #	Color	Putup Type	Length	UPC/EAN
5302UE.00152	Chrome	Reel	152 m	8719605008268
5302UE.00305	Chrome	Reel	305 m	8719605008275
5302UE 0081000	Gray			612825336853
5302UE 008500	Gray			612825336860
5302UE 008C250	Gray			
5302UE 008U1000	Gray			612825159612

5302UE 008U500	Gray			612825159629
5302UE.00U305	Gray	Reel	305 m	8719605008282

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.223 Revision Date: 06-24-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[5302UE 008U1000](#) [5302UE 008U500](#) [5302UE 008500](#) [5302UE 0081000](#) [5302UE 008C250](#)