



Product: [5308UE](#)

Security & Sound, #18-10c, BC, CMR

**Product Description**

Security & Sound Cable, Riser-CMR, 10-18 AWG stranded bare copper conductors with polypropylene insulation, PVC jacket with ripcord

**Technical Specifications**

**Product Overview**

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls
------------------------	---

**Construction Details**

**Conductor**

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	10	18 AWG	7x26	BC - Bare Copper

**Insulation**

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PO - Polyolefin	0.009 in (0.23 mm)	0.062 in (1.6 mm)	Black, Red, White, Green, Brown, Blue, Orange, Yellow, Purple, Gray

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.018 in (0.46 mm)	0.284 in (7.21 mm)	Yes

Overall Cable Diameter (Nominal):	0.284 in (7.21 mm)
-----------------------------------	--------------------

**Electrical Characteristics**

**Electricals**

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	6.5 Ohm/1000ft	30 pF/ft (98 pF/m)	9.8 Amps per conductor @ 25°C

**Voltage**

UL Voltage Rating
300 V

**Mechanical Characteristics**

**Temperature**

UL Temperature	Operating
75°C	-20°C to +75°C

**Bend Radius**

Stationary Min.	Installation Min.
2.8 in (71 mm)	2.8 in (71 mm)

Max. Pull Tension:	224 lbs (102 kg)
Bulk Cable Weight:	67 lbs/1000ft

**Standards and Compliance**

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL 1666 Riser, IEEE 1202 FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark
Plenum Number:	6308UE

History

Update and Revision:	Revision Number: 0.452 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
5308UE.00305	Chrome	Reel	305 m	8719605008343	
5308UE 0081000	Gray			612825160045	C
5308UE 008500	Gray			612825160052	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[5308UE 0081000](#) [5308UE 008500](#)