



Product: [5340F1](#) 

Security & Sound, #18-2c, TC, Shielded, CMG-FPL-PLTC, Water-Blocked

Product Description
Security & Sound Cable, Rated-CMG-FPL-PLTC- 1-18 AWG stranded tinned copper pair with PVC insulation, Beldfoil® shield, Waterblocking tape, PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy & Wet Location, Below-Grade Duct
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	18 AWG	7x26	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.080 in (2.0 mm)	Black & Red

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	20 AWG (7x28) TC

Waterblocking:	Waterblock Tape
----------------	-----------------

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.037 in (0.94 mm)	0.262 in (6.65 mm)

Overall Cable Diameter (Nominal):	0.262 in (6.65 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Pair(s)	7 Ohm/1000ft	45 pF/ft (150 pF/m)	14 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-30°C to +105°C

Bend Radius

Stationary Min.	Installation Min.
2.6 in (66 mm)	2.6 in (66 mm)

Max. Pull Tension:	57 lbs (26 kg)
Bulk Cable Weight:	27 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEEE 1202 FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 760, Article 800
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.460 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
5340F1 0101000	Black	612825161134	C
5340F1 0103600	Black	612825381099	
5340F1 0103600	Black	612825381099	
5340F1 0103900	Black	612825381105	
5340F1 0103900	Black	612825381105	
5340F1 0105000	Black	612825381112	
5340F1 0105000	Black	612825381112	
5340F1 0021000	Red	612825161127	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[5340F1 0021000](#) [5340F1 0101000](#) [5340F1 0105000](#)