



Product: [6100UE](#)

Security & Sound, 2 Conductor 14 AWG BC, CL2P

Product Description

Security & Commercial Audio Cable, Plenum-CL2P, 2-14 AWG stranded (19x27) bare copper conductors with Flamarrest® insulation, Flamarrest® jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Intercom/PA Systems, Sound/Audio Systems
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	14 AWG	19x26	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.010 in (0.25 mm)	0.090 in (2.3 mm)	Black, White

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.210 in (5.33 mm)	Yes

Overall Cable Diameter (Nominal):	0.210 in (5.33 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	2.54 Ohm/1000ft	36 pF/ft (120 pF/m)	25 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation
75°C	0°C to +75°C	0°C To +75

Bend Radius

Stationary Min.	Installation Min.
2.1 in (53 mm)	2.1 in (53 mm)

Max. Pull Tension:	95 lbs (43 kg)
Bulk Cable Weight:	35 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, CL2P
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	5100UE

History

Update and Revision:	Revision Number: 0.552 Revision Date: 02-15-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
6100UE 010500	Black	Reel	500 ft	612825173397	C
6100UE 010Z500	Black	ReelTuff Box	500 ft	612825173410	
6100UE 010U1000	Black	UnReel	1,000 ft	612825423423	
6100UE 010Z1000	Black	ReelTuff Box	1,000 ft	612825445371	
6100UE 008U1000	Gray	UnReel	1,000 ft	612825423409	
6100UE 008Z1000	Gray	ReelTuff Box	1,000 ft	612825173373	
6100UE 0081000	Gray	Reel	1,000 ft	612825173366	
6100UE 877500	Natural	Reel	500 ft	612825173427	
6100UE 8771000	Natural	Reel	1,000 ft	612825339519	C
6100UE 877U1000	Natural	UnReel	1,000 ft	612825423430	
6100UE 877Z1000	Natural	ReelTuff Box	1,000 ft	612825173434	
6100UE 8775000	Natural	Reel	5,000 ft	612825339502	
6100UE 009U250	White	UnReel	250 ft	612825377047	
6100UE 009U500	White	UnReel	500 ft	612825423416	
6100UE 009U500	White	UnReel	500 ft	612825423416	
6100UE 009Z500	White	ReelTuff Box	500 ft	612825173403	
6100UE 009U1000	White	UnReel	1,000 ft	612825173380	
6100UE 009Z1000	White	ReelTuff Box	1,000 ft	612825445364	
6100UE 004U1000	Yellow	UnReel	1,000 ft	612825416616	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[6100UE 877U1000](#) [6100UE 8771000](#) [6100UE 877500](#) [6100UE 8775000](#) [6100UE 008U1000](#) [6100UE 009U1000](#)
[6100UE 010U1000](#) [6100UE 004U1000](#) [6100UE 009U250](#) [6100UE 009U500](#) [6100UE 010500](#)