



Product: [6201FE](#)

Security & Sound, 3 Conductor 16 AWG BC, Shielded, CMP

Product Description

Security & Commercial Audio Cable, 3 Conductor 16 AWG stranded (19x29) bare copper conductors with Flamarrest® insulation, Beldfoil® shield, Plenum-CMP, Flamarrest® jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security Systems, Intercom/PA Systems, Sound/Audio Systems, Power Limited Controls
------------------------	--

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	16 AWG	19x29	BC - Bare Copper

Insulation			
Element	Material	Nom. Thickness	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.009 in (0.23 mm)	Black, Red, White

Outer Shield			
Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket			
Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.195 in (4.95 mm)	Yes
Overall Cable Diameter (Nominal):		0.195 in (4.95 mm)	

Electrical Characteristics

Electricals				
Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	4 Ohm/1000ft (13 Ohm/km)	81.5 pF/ft (267 pF/m)	146.7 pF/ft (481.3 pF/m)	6.25 Amps per conductor @ 25°C

Voltage	
UL Voltage Rating	
300 V (CMP)	

Mechanical Characteristics

Temperature	
UL Temperature	Operating
75°C	0°C to +75°C

Bend Radius	
Stationary Min.	Installation Min.
2.0 in (51 mm)	2.0 in (51 mm)

Max. Pull Tension:	116 lbs (52.6 kg)
Bulk Cable Weight:	36 lbs/1000ft (54 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
Non-Plenum Number:	5201FE

History

Update and Revision:	Revision Number: 0.355 Revision Date: 11-09-2022
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
6201FE 877500	Natural	Reel	500 ft	612825174158	
6201FE 8771000	Natural	Reel	1,000 ft	612825174172	C
6201FE 877U1000	Natural	UnReel	1,000 ft	612825427100	
6201FE 877Z1000	Natural	ReelTuff Box	1,000 ft	612825174189	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[6201FE 877500](#) [6201FE 8771000](#)