



Product: [6524UE](#)

Security & Sound, #22-6c, BC, CMP

Product Description

Security & Sound Cable, Plenum-CMP 6-22 AWG solid bare copper conductors with Flamarrest® insulation, Flamarrest® jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls
------------------------	---

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	No. of Conductors
22	Solid	BC - Bare Copper	6
Conductor Count:		6	

Insulation		
Material	Material Trade Name	Nominal Wall Thickness
PVC - Polyvinyl Chloride	Flamarrest®	0.009 in

Color Chart

Color
Black
Red
White
Green
Brown
Blue

Outer Shield

Material
No Shield

Outer Jacket

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	Flamarrest®	0.162 in	0.015 in	Yes

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
15.7 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
25 pF/ft

Current

Max. Recommended Current [A]
2 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Operating Temperature Range:	0°C To +75°C
------------------------------	--------------

Mechanical Characteristics

Bulk Cable Weight:	21.5 lbs/1000ft
Max. Pull Tension:	46.8 lbs
Min. Bend Radius/Minor Axis:	1.6 in

Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262 Plenum Flame Test (UL910)
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Related Part Numbers

Non-Plenum Number:	5524UE
--------------------	--------

Variants

Item #	Color	UPC
6524UE 877C500	Natural	612825353676
6524UE 877U1000	Natural	612825178187

History

Update and Revision:	Revision Number: 0.300 Revision Date: 05-05-2023
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[6524UE 877C500](#)