



Product: [7429W](#)

MachFlex™, 24+1G C #16 Str BC, PVC-NYL Ins, TPE Jkt, 1000V WTTC, 600V TC-ER

[Request Sample](#)

Product Description

MachFlex™ for High Flex, 24+1G Conductor 16AWG (26x30) Bare Copper, PVC-NYL Insulation, TPE Outer Jacket, 1000V WTTC, 600V TC-ER

Technical Specifications

Product Overview

Suitable Applications:	Robotics, Robot, Continuous Flex
------------------------	----------------------------------

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	24	16 AWG	26x30	BC - Bare Copper
Ground Wire	1	16 AWG	26x30	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC/Nylon - Polyvinyl Chloride + Nylon	0.021 in (0.53 mm)	0.101 in (2.57 mm)	Black and Numbered
Ground Wire	PVC/Nylon - Polyvinyl Chloride + Nylon	0.021 in (0.53 mm)	0.101 in (2.57 mm)	Green/Yellow

Outer Shield

Material
No Shield

Outer Jacket

Separator	Material	Nom. Thickness	Nom. Diameter
non-Woven Tape	TPE - Thermoplastic Elastomer	0.063 in (1.6 mm)	0.752 in

Overall Cable Diameter (Nominal):	0.752 in
-----------------------------------	----------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Max. Current
Conductor(s)	4.2 Ohm/1000ft	8 Amps per Conductor at 25°C
Ground Wire	4.45 Ohm/1000ft (14.6 Ohm/km)	

Voltage

UL Voltage Rating
1000 V (WTTC), 600 V (TC-ER)

Mechanical Characteristics

Temperature

UL Temperature	Operating
UL : 90°C Dry, 75°C Wet; AWM 20328 : 105°C	-40°C To +105°C

Bend Radius

Stationary Min.	Installation Min.
3.01 in (76.5 mm)	3.76 in

Max. Pull Tension:	1000 lbs (450 kg)
Bulk Cable Weight:	371 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Outdoor, Sunlight Resistance, UV Resistance, Oil Resistance
Flammability / Reaction to Fire:	UL1685 UL Loading, IEEE 1202 FT4
NEC / UL Compliance:	Article 336
AWM Compliance:	AWM 20328, AWM I/II A/B
CEC / C(UL) Compliance:	CIC, TC
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.301 Revision Date: 01-10-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
7429W 060250	Chrome	Reel	250 ft	612825186496	C
7429W 0601000	Chrome	Reel	1,000 ft	612825186489	
7429W 0605000	Chrome	Reel	5,000 ft	612825186502	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[7429W 0601000](#) [7429W 060250](#)