


**Product:** [7952A](#) 

## Composite Data, Audio, Video, Security and Control Cable



### Product Description

Siamese Construction Composite - (1)Cat 5 4-pair 24 AWG unshielded plus (4) 14 AWG stranded (104x34) bare copper conductors, polyolefin Insulation on all conductors, overall F-R PVC jacket, sequentially marked, CMR rated.

### Technical Specifications

#### Product Overview

Suitable Applications:	Data, control
------------------------	---------------

#### Physical Characteristics (Overall)

Conductor Count:	12
Total Number of Pairs:	4

#### Temperature Range

Installation Temp Range:	0°C to +75°C
UL Temp Rating:	60°C
Operating Temp Range:	-20°C to +75°C

#### Mechanical Characteristics

Bulk Cable Weight:	94 lbs
Max. Pull Tension:	200 lbs

#### Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	Yes

#### Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes

#### Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1666 Vertical Shaft
CSA Flammability:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Put-Up Type	Length	UPC
7952A 337500	Green, Light	Reel	500 ft	612825001706

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.69 Revision Date: 12-15-2021
----------------------	---

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[7952A 337500](#)