



## Product: [8024](#)

### Bus Bar Wire, #28 Sol TC

 [Request Sample](#)

#### Product Description

Bus Bar Wire, 28AWG (Solid) Tinned Copper, QQ-W-343G

#### Technical Specifications

##### Product Overview

Suitable Applications:	bus bar
------------------------	---------

##### Physical Characteristics (Overall)

###### Conductor

AWG	Stranding	Material	No. of Conductors
28	Solid	TC - Tinned Copper	1

Conductor Count: 1

##### Construction and Dimensions

Circular Mil Area (CMA):	164
--------------------------	-----

##### Electrical Characteristics

###### Conductor DCR

Nominal Conductor DCR
66.7 Ohm/1000ft

##### Mechanical Characteristics

Bulk Cable Weight:	1 lbs/1000ft
--------------------	--------------

##### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

##### Flammability, LS0H, Toxicity Testing

UL voltage rating:	N/A
--------------------	-----

##### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
8024 000100	None	Reel	100 ft	612825194408
8024 0001000	None	Reel	1,000 ft	612825194415

### History

Update and Revision:

Revision Number: 0.280 Revision Date: 07-26-2020

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8024 000100](#) [8024 0001000](#)