



Product: [8737](#)

Audio Cable, #22-1pr, TC, O/A Braid, CM

Product Description

22 AWG stranded (7x30) tinned copper conductors, PVC insulation, twisted pair, tinned copper spiral wrapped shield (85% coverage), PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Construction Details

Conductor

Size	Stranding	Material
22	7x30	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.06 in (1.5 mm)	Black & Red

Outer Shield

Shield Type	Material	Coverage
Spiral Serve / Screen	Tinned Copper (TC)	85%

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.025 in (0.64 mm)	0.18 in

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
16 Ohm/1000ft (52 Ohm/km)	40 pF/ft (130 pF/m)	70 pF/ft (230 pF/m)	49 Ohm	66%	3 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
80°C	-20°C To +80°C

Max. Pull Tension:	20 lbs (9.1 kg)
Bulk Cable Weight:	18 lbs/1000ft (27 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, 1202
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	CMG
AWM Compliance:	AWM 2095 (300 V 80°C)
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.421 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8737 060500	Chrome	Reel	500 ft	612825214847	
8737 060U500	Chrome	UnReel	500 ft	612825215103	
8737 0601000	Chrome	Reel	1,000 ft	612825214830	C
8737 060U1000	Chrome	UnReel	1,000 ft	612825214816	
8737 0605000	Chrome	Reel	5,000 ft	612825214809	C

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8737 060500](#) [8737 060U1000](#) [8737 060U500](#) [8737 0601000](#) [8737 0605000](#)