

8767 Multi-Conductor - Audio, Control and Instrumentation Cable

For more Information
please call

1-800-Belden1

**General Description:**

22 AWG solid conductors, PVC insulation, tinned copper, twisted pairs, individually shielded w/Beldfoil® (100% coverage), 22 AWG solid TC drain wire, overall PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material
3	22	Solid	TC - Tinned Copper

Total Number of Conductors:

6

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.013

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding:

Solid

Inner Shield Drain Wire Conductor Material:

TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.037

Overall Cable

Overall Nominal Diameter:

0.279 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green

Mechanical Characteristics (Overall)

Operating Temperature Range:

-20°C To +80°C

UL Temperature Rating:

80°C (UL AWM Style 2464)

Bulk Cable Weight:

42 lbs/1000 ft.

Max. Recommended Pulling Tension:

87 lbs.

Min. Bend Radius/Minor Axis:

3 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:

CMG, MPG

CEC/C(UL) Specification:

CMG, MPG

AWM Specification:

UL Style 2464 (300 V 80°C)

EU Directive 2011/65/EU (ROHS II):

Yes

8767 Multi-Conductor - Audio, Control and Instrumentation Cable

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 FT4 Loading

CSA Flame Test: FT4

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/ft)

.19

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

40

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

77

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

16.7

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 12 Ohm/1000 ft

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

2 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8767 060U500	500 FT	22.500 LB	CHROME		3 PR FS #22 PVC PVC
8767 0601000	1,000 FT	46.000 LB	CHROME	C	3 PR FS #22 PVC PVC
8767 060500	500 FT	23.000 LB	CHROME		3 PR FS #22 PVC PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 10-05-2012

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[8767 0601000](#) [8767 060U500](#) [8767 060500](#)