



Product: [8790](#)

Line Level Audio Cable, 1 Pr #18 Str TC, 85% TC Spiral Serve, PVC Jkt, CMG

Product Description

Line Level Audio Cable, 1 Pair 18 AWG (7 x 26) Tinned Copper PVC insulation, 85% Tinned Copper Spiral Serve/Screen, PVC Jacket, CMG

Technical Specifications

Product Overview

Suitable Applications:	Line level audio; Low voltage analog signals and control
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	18 AWG	7x26	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.022 in (0.56 mm)	0.090 in (2.3 mm)	Red & White

Outer Shield

Shield Type	Material	Coverage
Spiral Serve / Screen	Tinned Copper (TC)	85%

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.028 in (0.71 mm)	0.241 in (6.12 mm)

Overall Cable Diameter (Nominal):	0.241 in (6.12 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Pair(s)	7.2 Ohm/1000ft	53 pF/ft (170 pF/m)	92 pF/ft (300 pF/m)	41 Ohm	65%	8 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V (CMG)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-20°C to +60°C

Bend Radius

Stationary Min.	Installation Min.
2.4 in (61 mm)	2.4 in (61 mm)

Max. Pull Tension:	45 lbs (20 kg)
Bulk Cable Weight:	31 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEEE 1202, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.459 Revision Date: 02-15-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8790 060500	Chrome	Reel	500 ft	612825216469	C
8790 060U500	Chrome	UnReel	500 ft	612825216568	
8790 0601000	Chrome	Reel	1,000 ft	612825216452	C
8790 060U1000	Chrome	UnReel	1,000 ft	612825216438	
8790 0605000	Chrome	Reel	5,000 ft	612825216421	C

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8790 060U500](#) [8790 060U1000](#) [8790 060500](#) [8790 0601000](#)