



Product: [9452](#)

Microphone Cable, 2C #24 Str TC, Noise reducing tape, O/A Foil, PVC Jacket

Product Description

Microphone Cable, 2 Conductor 24 AWG (19 x 36) Tined Copper (High conductivity), PE Insulation, Noise reducing tape, Overall Beldfoil® Shield, PVC Jacket

Technical Specifications

Product Overview

Suitable Applications:	Low frequency microphone or musical instruments; Balanced analog audio; Low Noise for high-EMI environments
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	24 AWG	19x36	TC - Tinned Copper (High Conductivity)

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code	Notes
Conductor(s)	PE - Polyethylene	0.008 in (0.20 mm)	0.04 in (1.0 mm)	Black, Red	HDPE

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Textile (Conductive)	100%	24 AWG (19x36) TC
Tape	Bi-Laminate (Alum+Poly)	100%	

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.020 in (0.51 mm)	0.135 in (3.43 mm)

Overall Cable Diameter (Nominal):	0.135 in (3.43 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Max. Current
Conductor(s)	28.8 Ohm/1000ft	30 pF/ft (98 pF/m)	58 pF/ft (190 pF/m)	56 Ohm	2.8 Amps per conductor @ 25°C

Voltage

UL Voltage Rating	Voltage Rating
200 V	200 V

Mechanical Characteristics

Temperature

Operating
-40°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
-----------------	-------------------

1.6 in (41 mm)	1.6 in (41 mm)
Max. Pull Tension:	29 lbs (13 kg)
Bulk Cable Weight:	11 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
CPR Compliance:	CPR Euroclass: Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.474 Revision Date: 02-15-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
9452 010500	Black	Reel	500 ft	612825253174
9452 010U500	Black	UnReel	500 ft	612825254027
9452 0101000	Black	Reel	1,000 ft	612825253204
9452 010U1000	Black	UnReel	1,000 ft	612825253181

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9452 010U500](#)