



Product: [9794](#)

Electronic, 4 C #22 Sol BC, PO Ins, PVC Jkt, CM

[Request Sample](#)

Product Description

Electronic, 4 Conductor 22AWG (Solid) Bare Copper, PO Insulation, PVC Outer Jacket, CM

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
22	Solid	BC - Bare Copper	4

Conductor Count:	4
------------------	---

Insulation

Material	Nominal Wall Thickness
PE - Polyethylene	0.018 in

Color Chart

Color
Green
Red
Yellow
Black

Outer Shield Material

Material
No Shield

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.2 in	0.025 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
16 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
16 pF/ft

Inductance

Nominal Inductance
0.22 μ H/ft

Delay

Max. Delay Skew

66 ns/100m

Current

Max. Recommended Current [A]

2.4 Amps per Conductor at 25°C

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

UL Temp Rating:	60°C (UL AWM Style 2094)
Operating Temp Range:	-30°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	24.8 lbs/1000ft
Max. Pull Tension:	31 lbs
Min Bend Radius/Minor Axis:	2 in

Standards

NEC/(UL) Compliance:	CM
UL AWM Style Compliance:	UL Style 2094 (300 V 60°C)
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading
IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC
9794 6065000	Gray, Rose	612825258704
9794 6061000	Rose Gray	612825258698

Footnote: C - CRATE REEL PUT-UP.

History

Update and Revision:	Revision Number: 0.282 Revision Date: 06-24-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9794 6061000](#) [9794 6065000](#)