



Product: [9928](#)

Lead Wire, #28 Str TC, PVC Ins, AWM 1007 AWM 1569

[Request Sample](#)

Product Description

Low Temp Plastic Lead Wire, 28AWG (7x36) Tinned Copper, PVC Insulation, AWM 1007 AWM 1569 CSA TYPE TR-64 TRSR-64

Technical Specifications

Product Overview

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, internal wiring of appliances
------------------------	---

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	No. of Conductors
28	7x36	TC - Tinned Copper	1
Conductor Count:			1

Insulation			
Material	Nominal Diameter	Nominal Wall Thickness	Min. Average Wall Thickness
PVC - Polyvinyl Chloride	0.047 in	0.016 in	0.015 in

Electrical Characteristics

Voltage	
UL Voltage Rating	
300 V RMS	

Temperature Range

Non-UL Temp Rating:	105°C
UL Temp Rating:	105°C

Mechanical Characteristics

Bulk Cable Weight:	1.5 lbs/1000ft
Min. Bend Radius/Minor Axis:	0.19 in

Standards

UL Rating:	300V RMS, 80°C and 300V, 105°C
UL AWM Style Compliance:	AWM 1007, AWM 1569
CSA Rating:	300V RMS, 105°C
CSA Type:	TRSR-64

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes

EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
CSA Flammability:	FT1
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
9928 010100	Black	Reel	100 ft	612825264064
9928 0101000	Black	Reel	1,000 ft	612825264071
9928 013100	Blue, Dark	Reel	100 ft	612825264088
9928 0131000	Blue, Dark	Reel	1,000 ft	612825264095
9928 001100	Brown	Reel	100 ft	612825263920
9928 0011000	Brown	Reel	1,000 ft	612825263937
9928 0081000	Gray	Reel	1,000 ft	612825264033
9928 005100	Green, Dark	Reel	100 ft	612825264002
9928 0051000	Green, Dark	Reel	1,000 ft	612825264019
9928 003100	Orange	Reel	100 ft	612825263968
9928 0031000	Orange	Reel	1,000 ft	612825263975
9928 002100	Red	Reel	100 ft	612825263944
9928 0021000	Red	Reel	1,000 ft	612825263951
9928 007100	Violet	Reel	100 ft	612825264026
9928 009100	White	Reel	100 ft	612825264040
9928 0091000	White	Reel	1,000 ft	612825264057
9928 004100	Yellow	Reel	100 ft	612825263982
9928 0041000	Yellow	Reel	1,000 ft	612825263999

Footnote:	P - STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M= FOR 1 OR 2 STRIPES. 10,000' MINIMUM ORDER FOR COLOR COMBINATION. PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL, WITH A MINIMUM LENGTH OF 100'.
-----------	---

History

Update and Revision:	Revision Number: 0.369 Revision Date: 05-05-2023
----------------------	--

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9928 0131000](#) [9928 0021000](#) [9928 0081000](#) [9928 009100](#) [9928 001100](#) [9928 0091000](#) [9928 013100](#) [9928](#)
[0011000](#) [9928 0031000](#) [9928 003100](#) [9928 0101000](#) [9928 007100](#) [9928 005100](#) [9928 004100](#) [9928 0051000](#)
[9928 002100](#) [9928 010100](#) [9928 0041000](#)