



4- and 8-Ports

4- and 8-Ports

4-Ports



8-Ports



Pin Assignments

M12

Wiring Diagrams



4-Ports

- 1 = brown (+)
2 = n.a.
3 = blue (-)
4 = white (1)
green (2)
yellow (3)
grey (4)
5 = green/yellow (PE)



8-Ports

- 1 = brown (+)
2 = n.a.
3 = blue (-)
4 = white (1)
green (2)
yellow (3)
grey (4)
pink (5)
red (6)
black (7)
violet (8)
5 = green/yellow (PE)



M12 Rugged Distribution Boxes, One Signal Per Socket, with or without LED

Technical Data

Environmental Conditions

Degree of protection	IP65 / IP67
Pollution severity	3
Operating temperature range	-40°C / +80°C (dragchain and UL max. 60°C)

Materials

Contact	CuZn, pre-nickel and gold-plated
Contact bearer	TPU-GF
Housing	Zinc die casting
O-ring	FKM

Electrical Data

Rated voltage	30 V
Rated current*	4 A per outlet / 8 A max. total; at 40°C
Rated impulse voltage	32 V
Contact resistance	≤5mΩ
Insulation resistance	> 10 ⁹ Ω

* only in locked position with its proper counterparts or dust covers

Additional Technical Data

operation display: LED Green
Function display / channel status:
LED Channel A: Yellow
LED Channel B: White

Cable Specifications

Cable No.	Outer Jacket	Conductor Size	Color	Outside Diameter
328	PUR, halogen-free	3 x 0.75 mm ² 4 x 0.34 mm ²	Black	.268" (6.8 mm)
331	PUR, halogen-free	3 x 0.75 mm ² 8 x 0.34 mm ²	Black	.315" (8.0 mm)

Part Number	Ports	Standard Cable Length	Characteristics
ASB-R 4 5-4-328/...M	ASB-R 4/LED 5-4-328/...M	4	5M and 10M
ASB-R 8 5-4-331/...M	ASB-R 8/LED 5-4-331/...M	8	5M and 10M



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

[ASB-R 4 5-4-328/10 M](#) [ASB-R 4 5-4-328/5 M](#) [ASB-R 4/LED 5-4-328/10 M](#) [ASB-R 4/LED 5-4-328/5 M](#) [ASB-R 8 5-4-331/10 M](#) [ASB-R 8 5-4-331/5 M](#) [ASB-R 8/LED 5-4-331/10 M](#) [ASB-R 8/LED 5-4-331/15 M](#) [ASB-R 8/LED 5-4-331/5 M](#)