

AX102906 Faceplates and Panels - KeyConnect Video F Coax, Surface



For more Information
please call

1-800-Belden1



General Description:

KeyConnect Video F, Coax, Surface

Usage (Overall)

Suitable Applications:	- Coax
Related Parts:	- Compatible KeyConnect-style Faceplate and Patch Panel

Physical Characteristics (Connectivity)

Capacity Access

Front Connection:	Flush
-------------------	-------

Dimensions

Dimensions:

Height (mm)	Width (mm)	Depth (mm)
21.590	17.526	29.972

Materials

Materials:

Description	Material
Insert	Plastic - UL94V-0

Color

Color:	Almond
--------	--------

Weight

Weight:	0.015 kg
---------	----------

Packaging

Packaging:	10 units packaged in a plastic bag.
------------	-------------------------------------

Mechanical Characteristics (Connectivity)

Footprint/Type:	KeyConnect
Connector/Hardware Retention:	88.964 N
Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006
MIL Order #39 (China RoHS):	Yes
Safety Listing:	Bi-national Standard Listed

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For proper installation refer to Installation Guide PX103826. Visit our web site at <http://www.belden.com>

Product Family

Part Numbers:

Item Number	Color
AX102906	Almond

METRIC MEASUREMENT VERSION

AX102906 Faceplates and Panels - KeyConnect Video F Coax, Surface

AX102907	Elec. White
AX102908	Black
AX104567	Ivory
AX105384	Dark Gray

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX102906	1 EA	0.015 KG			KCONN F-COAX MODULE ALM

Revision Number: 0 Revision Date: 08-14-2012

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[AX102906](#)