



Part Number: FI4B004PBA

Indoor Plenum OM4 Breakout 4F 2mm Sub-Units Aqua

Product Description

Indoor OM4 Breakout 4 Fibers OFNP Sub-Units (2.0mm) Aqua Jacket

Technical Specifications

Product Overview

Part Number:	FI4B004PBA
Construction Type:	Breakout
Environmental Space:	Indoor
Suitable Applications:	Indoor

Construction

Fiber Cable Construction

Fiber Type	Fiber Count
OM4	4

Fiber Type:	OM4
Fiber Count:	4
Fiber Color Coding:	Blue, Orange, Green, Brown

Buffer Specification

Fiber Type	Buffer Diameter
OM4	900 μ m

Bulk Cable Weight:	29 lbs/1000ft
--------------------	---------------

SubUnit Specifications

Fibers Per Subunit:	1
SubUnit Diameter:	0.078 in

Jacket Specifications

Outer Jacket Material

Nominal Diameter
0.26 in (6.6 mm)

Outer Jacket Color:	Aqua
Number of Outer Jacket Ripcords:	2

Optical Characteristics

Effective Modal Bandwidth (EMB):	4700 MHz-km / 500 MHz-km
Fiber Core Diameter:	50/125 μ m
Max Attenuation at 1300 nm:	1.2 dB/km
Max Attenuation at 850 nm:	3.0 dB/km
Wavelength:	850 nm / 1300 nm
10 Gigabit Ethernet Performance:	550 m / 300 m
1 Gigabit Ethernet Performance:	- / 550 m
Min Overfilled Launch (OFL) Bandwidth:	3500 MHz-km / 550 Mhz-km

Mechanical Characteristics

Min Bend Radius During Installation:	20x Cable OD
Min Bend Radius During Operation:	10x Cable OD
Max Tensile Strength During Installation:	78 N (345 lbf)
Max Tensile Strength During Operation:	38 N (170 lbf)

Temperature Range

Storage Temp Range:	-40C to +70C
---------------------	--------------

Standards

UL Rating/Flame Test:	Plenum
NEC/(UL) Specification:	OFNP
Telecommunications Standards:	ANSI/ICEA S-83-596
RoHS:	Yes

History

Variants

Item #	Color
F14B004PBA	Aqua

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[FI4B004PBA](#)