



Product: [DB58BNC](#)

Double Bubble RG-58 BNC Coax Compression Connector

Product Description

Double Bubble RG58 BNC connector, fits standard RG58 50 Ohm coaxial cable. Compression design that molds the metal completely around the cable. 25 per Pack

Technical Specifications

Product Overview

Suitable Applications:	Antenna, 50 Ohm
------------------------	-----------------

Physical Characteristics (Overall)

Packaging:	25 Pack
Number of Pieces:	1

Connectors

Materials

Material
Nickel plated Brass
Gold Plated

Electrical Characteristics

Impedance

Nominal Characteristic Impedance
50 Ohm

Mechanical Characteristics

Footprint/Type:	Coax
Connector Interface Type:	BNC
Gender:	Male - plug
Connector Series Name:	Double Bubble
Locking:	No
Tool Compatibility:	CPLCRBC-BR (compression)
Termination Type:	Compression
Cable Center Conductor Diameter Limits:	.0317 - .0339 inch
Cable Dielectric Diameter Limits:	.0111 - .121 inch
Cable Outer Jacket Diameter Limits:	.185 - .201 inch

Standards

RG Type:	58
----------	----

Applicable Environmental and Other Programs

EU CE Mark:	Yes
-------------	-----

Related Part Numbers

Variants

Item #	Color	UPC
DB58BNC	No Color	845671002140

Footnote:	Q - STANDARD PACKAGES CANNOT BE BROKEN.
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

History

Update and Revision:	Revision Number: 0.114 Revision Date: 03-04-2023
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[DB58BNC](#)