



Be Certain with Belden

DeviceNet Thin Cables

0935 253 301 | 0935 253 302 | 0935 253 303



0935 253 301/... M:

Double-ended with 7/8" male connector and 7/8" female connector, 5 poles

0935 253 302/... M:

Single-ended with 7/8" male connector, 5 poles

0935 253 303/... M:

Single-ended with 7/8" female connector, 5 poles

Electrical

Current rating 4 A
Voltage rating 250 V

Pin Assignment

male connector / female connector, 5 poles	Function	Color
Pin 1	Shield	
Pin 2	+ 24 V	red
Pin 3	GND (0 V)	black
Pin 4	CAN_H	white
Pin 5	CAN_L	blue

Part Number	Standard Cable Lengths	
0935 253 301/...M	1 M 3 M 5 M	  
0935 253 302/...M	1 M 3 M 5 M	  
0935 253 303/...M	1 M 3 M 5 M	  

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumberg Automation:](#)

[0935 253 301/1 M](#) [0935 253 302/3 M](#) [0935 253 303/3 M](#) [0935 253 303/1 M](#) [0935 253 301/5 M](#)