

Product: ISPECCGPS-8M-TL ☑



SPE T1 industrial connector, crimp, plastic housing, IP20, male, 2-ple, SPE-8M, shielded, straight

Product Description

SPE T1 industrial connector, crimp, plastic housing, IP20, male, 2-ple, SPE-8M, shielded, straight, 0.08 ... 0.32 mm², AWG 22 ...AWG28

Technical Specifications

Technical Data

Product Family:	SPE Field Attachables
Product Sub Family:	SPE Field Attachable T1 Industrial
Brand:	Lumberg Automation
Connector Type:	Field attachable
Type of Contact / Gender:	male
Connector Design:	straight
Number of Pins:	2
Coding:	SPE-2P-L
Attachment Type:	Latching Locking
Test Voltage Contact - Contact:	1 kV
Test Voltage Contact - Ground:	2.25 kV
Operating Voltage:	50 V AC / 60 V DC
Rated Current*:	4 A
Contact Resistance:	20 mOhm
Mating Cycles:	≥ 1,000
Type of Connection:	Crimp
Strain-Relief:	clamping cage
Suitable Cables:	Ø4.5Ø6 mm
Ambient Temperature (Operation)*:	-40°C to +85°C
Protection Degree / IP Rating**:	IP20
Transmission characteristics:	4 GHz
Data Rate:	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s

Materials

Housing Material:	Plastic
Housing Color:	Black

Additional Technical Data

Fastening Torque (Attachment):	30 Ncm, hand-tight

Safety & Environmental Compliance

RoHS Compliant:	Yes		
-----------------	-----	--	--

Notes

Note Derating:	* Notice derating	
Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.	ı

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

ISPECCGPS-8M-TL