


Product: [KEYCONNECT STAINLESS DG FP](#) 



KeyConnect Stainless Steel, Double-Gang Faceplate

Product Description

KeyConnect Stainless Steel, Double-Gang Faceplate, Compatible with KeyConnect style modular jacks

Technical Specifications

Product Overview

Suitable Applications:	Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400, 1200, fiber and coax
------------------------	--

Physical Characteristics (Overall)

Height:	4.5 m
Width:	4.59
Depth:	0.26
Front Connection:	Flush
Packaging:	Individually packaged in a plastic bag.
Weight:	0.06 kg

Connectors

Materials

Material
Stainless Steel

Temperature Range

Installation Temp Range:	-10 to 60°C
Storage Temp Range:	-40 to 70°C
Operating Temp Range:	-10 to 60°C

Mechanical Characteristics

Footprint/Type:	KeyConnect
Connector/Hardware Retention:	20 lbs

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	Bi-national Standard Listed
-----------------	-----------------------------

Part Number

Related Parts:	Compatible with 10GX, CAT6+ and CAT5E KeyConnect Modular Jacks and KeyConnect Multimedia Modules
----------------	--

Variants

Item #	Color	Port Count
--------	-------	------------

AX102011	Stainless Steel	4 Port
AX102012	Stainless Steel	6 Port
AX102013	Stainless Steel	12 Port
AX104234	Stainless Steel	12 Port
AX104479	Stainless Steel	4 Port
AX104480	Stainless Steel	6 Port

Product Notes

Included Parts:	6-32 screw
Notes:	For proper installation refer to Installation Guide PX103826. Visit our web site at http://www.belden.com

History

Update and Revision:	Revision Number: 0.160 Revision Date: 03-16-2021
----------------------	--

© 2021 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[AX102011](#)