

Product: [MDVO BNC COAXIAL MODULE](#) 

MDVO BNC Coaxial Module, 1-Port



Product Description

MDVO BNC Coaxial Module, 1-Port, Available in several colors.

Technical Specifications

Product Overview

Suitable Applications:	BNC
------------------------	-----

Physical Characteristics (Overall)

Height:	0.63 m
Width:	0.63
Depth:	1.282
Packaging:	10 units packaged in a plastic bag.
Weight:	0.021 lbs

Connectors

Materials

Material
Plastic - UL94V-0, Metal

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	MDVO
Connector/Hardware Retention:	20 lbs

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Part Number

Related Parts:	Compatible MDVO-style Faceplate and Patch Panel
----------------	---

Variants

Item #	Color	UPC
A0406996	Almond	611589000444

A0406998	Black	611589000468
A0406995	Gray	611589000437
AX102598	Ivory	611589027694
A0406997	White	611589000451

Product Notes

Notes:	For proper installation refer to Installation Guide P0749391. Visit our web site at <a href="http://www.belden.com">http://www.belden.com</a>
--------	---

History

Update and Revision:	Revision Number: 0.166 Revision Date: 03-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[A0406997](#)