

Mini Single-Ended Cordsets

RK 30-838



Description

MINI, Single-Ended Cordset, Straight, Female, 3 Pole, 16 AWG, PLTC, Yellow. TPE Cable, U.S. Color Code, IP 67 and NEMA 6P Rated.

Technical Data

Material

TPU, yellow Molded body

Coupling nut Aluminum, anodized black Contacts Brass, gold plated

Insert TPE, yellow

Electrical

Current rating 8 A Voltage rating 600 V

Mechanical


-30°C to + 90°C Temperature IP 67, NEMA 6P rated Protection


Cable

Jacket PUR, Yellow 16 AWG Gauge TC-ER Outside diameter .315"

Part Number

RK 30-838/1M	
RK 30-838/2M	
RK 30-838/3M	
RK 30-838/5M	
RK 30-838/10M	
RK 30-838/20M	





Pin Assignments

Face View 7/8"



1 = green

2 = black 3 = white













Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

<u>RK 30-838/10M</u> <u>RK 30-838/30M</u> <u>RK 30-838/3M</u> <u>RK 30-838/4M</u> <u>RK 30-838/50M</u> <u>RK 30-838/5M</u> <u>RK 30-838/6M</u> <u>RK 30-838/6M</u> <u>RK 30-838/6M</u> <u>RK 30-838/2M</u>