

RSRK 20...50 | RSRKW 20...50




Mini, 7/8"-Round-Plug Connector, Double-Ended Cordsets, IEC Color Code

2-, 3-, 4- and 5-Poles


Mini, 7/8" double-ended cordsets, male straight with external threads to female straight connector, 2-, 3-, 4-, and 5-poles with molded cable, IEC color code.

RSRK



Mini, 7/8" double-ended cordsets, male straight with external threads to female 90° connector, 2-, 3-, 4-, and 5-poles with molded cable, IEC color code.


RSRKW



Pin Assignments


Mini, 7/8" - Male / Female

2 poles




1 = brown
2 = blue

3 poles




1 = black
2 = brown
3 = blue

4 poles



Euro standard wiring
for active I/O modules


1 = brown
2 = white
3 = blue
4 = black



Standard wiring for
general US market

1 = black
2 = blue
3 = brown
4 = white

5 poles



1 = black
2 = blue
3 = yellow w/green tr.
4 = brown
5 = white

Be Certain with Belden

Cordsets Double-Ended



Mini, 7/8"-Round-Plug Connector, Double-Ended Cordsets, IEC Color Code RSRK 20...50 | RSRKW 20...50

Technical Data

Environmental

Degree of protection IP 67 / NEMA 6P
Operating temperature range -40°C (-40°F) / +90°C (194°F)

Mechanical

Housing / Molded body TPU, yellow
Insert TPU, yellow
Contact CuZn, gold over silver plated
Coupling nut Aluminum, anodized black

Electrical

Current rating 2-3 pole: 8 A
4-5 pole: 5.6 A
Voltage rating 300 V

Cable Specifications - IEC Color Code

Cable No.	Outer Jacket	Gauge	Jacket Color	OD	Temperature Rating	Agency Approvals
602	PUR	18AWG	Yellow	.230" (5.8 mm)	-40°C (-40°F) to +80°C (176°F)	UL: AWM 20233 / CSA: AWM I/II A/B
Continuous flex rating and suitable for general C-track usage. 1 million cycles at minimum bend radius 10X cable diameter.						
603	PVC	18AWG	Yellow	.290" (7.4 mm)	-40°C (-40°F) to +105°C (221°F)	UL: AWM 2661 / CSA: AWM I/II A/B
637	TPE	18AWG	Yellow	.280" (7.1 mm)	-40°C (-40°F) to +105°C (221°F)	UL: PLTC / CSA: AWM I/II A/B
645	PUR	18AWG	Yellow	.220" (5.6 mm)	-40°C (-40°F) to +80°C (176°F)	UL: AWM 20233 / CSA: AWM I/II A/B
731	TPE	18AWG	Yellow	.284" (7.2 mm)	-40°C (-40°F) to +90°C (194°F)	UL: PLTC / CSA: AWM I/II A/B
794	TPE	18AWG	Yellow	.304" (7.7 mm)	-40°C (-40°F) to +90°C (194°F)	UL: PLTC / CSA: AWM I/II A/B

Part Number		Pins	Outer Jacket	Standard Cable Lengths	Characteristics
RSRK 20-603/...M	RSRKW 20-603/...M	2	PVC	0.3 M / 0.6 M / 1 M / 2 M / 5 M	  
RSRK 30-731/...F	RSRKW 30-731/...F	3	TPE	6 F / 12 F / 15 F / 20 F / 30 F	     
RSRK 30-645/...M	RSRKW 30-645/...M		PUR	0.3 M / 0.6 M / 1 M / 2 M / 5 M	  
RSRK 40-637/...F	RSRKW 40-637/...F	4	TPE	6 F / 12 F / 15 F / 20 F / 30 F	     
RSRK 40-602/...M	RSRKW 40-602/...M		PUR	0.3 M / 0.6 M / 1 M / 2 M / 5 M	   
RSRK 50-794/...F	RSRKW 50-794/...F	5	TPE	6 F / 12 F / 15 F / 20 F / 30 F	     

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

[RSRK 40-602/2M](#) [RSRK 50-794/5M](#) [RSRK 50-794/2F](#) [RSRK 40-602/0.6M](#) [RSRK 40-637/15F](#) [RSRK 30-645/10M](#)
[RSRK 40-637/15M](#) [RSRK 40-637/2M](#) [RSRK 40-637/3F](#) [RSRK 50-794/60F](#) [RSRK 30-645/5M](#) [RSRK 40-602/1M](#)
[RSRK 50-794/30F](#) [RSRK 50-794/6F](#) [RSRK 20-603/0.6M](#) [RSRK 50-794/3F](#) [RSRK 20-603/0.3M](#) [RSRK 50-794/9F](#)
[RSRK 40-637/20F](#) [RSRK 30-645/2M](#) [RSRK 40-637/6F](#) [RSRK 50-794/7F](#) [RSRK 40-637/5M](#) [RSRK 30-731/6F](#) [RSRK](#)
[20-603/2M](#) [RSRK 30-731/20F](#) [RSRK 30-645/0.3M](#) [RSRK 40-637/1F](#) [RSRK 20-603/5M](#) [RSRK 40-637/60F](#) [RSRK 30-](#)
[645/0.6M](#) [RSRK 50-794/20M](#) [RSRK 40-637/10M](#) [RSRK 40-602/5M](#) [RSRK 50-794/3M](#) [RSRK 50-794/7M](#) [RSRK 50-](#)
[794/50F](#) [RSRK 40-637/12F](#) [RSRK 40-637/30F](#) [RSRK 50-794/70F](#) [RSRK 50-794/115F](#) [RSRK 40-602/0.3M](#) [RSRK](#)
[50-794/12F](#) [RSRK 50-794/20F](#) [RSRK 30-731/15F](#) [RSRK 50-794/40F](#) [RSRK 50-794/1.5F](#) [RSRK 50-794/15F](#) [RSRK](#)
[40-637/45F](#) [RSRK 40-637/40F](#) [RSRK 40-637/2F](#) [RSRK 50-794/10F](#) [RSRK 30-645/30M](#) [RSRK 50-794/1F](#) [RSRK 40-](#)
[602/10M](#) [RSRK 20-603/1M](#) [RSRK 30-731/12F](#) [RSRK 30-645/1M](#) [RSRK 50-794/2M](#) [RSRK 30-731/30F](#)