

Mini Double-Ended Cordsets

RSRK 30-838 | RSRK 40-839 | RSRK 50-877



Description

MINI, Double-Ended Cordset, Straight, Male (external threads) to Female (internal threads), 3-, 4- and 5-Pole, 16 AWG, Yellow TPE (TC-ER) Cable, U.S. Color Code, IP 68 and NEMA 6P Rated.

Technical Data

Material

Molded body Coupling nut PUR, yellow Aluminum, e-coated or

anodized black

Brass, gold over nickel plated

PUR, yellow

Contacts Insert

Electrical

8 A Current rating Voltage rating 600 V

Mechanical

Temperature Protection

-30°C to + 90°C IP 68, NEMA 6P

Cable

Jacket Gauge Yellow, TPE 16 AWG stranded copper

UL Approval TC-ER

Outside diameter 838: .315" 839: .342"

877: .371"

Part Number

| RSRK 30-838/1M | |
|-----------------|--|
| RSRK 30-838/2M | |
| RSRK 30-838/3M | |
| RSRK 30-838/5M | |
| RSRK 30-838/10M | |
| RSRK 30-838/20M | |
| RSRK 40-839/1M | |
| RSRK 40-839/2M | |
| RSRK 40-839/3M | |
| RSRK 40-839/5M | |
| RSRK 40-839/10M | |
| RSRK 40-839/20M | |
| RSRK 50-877/1M | |
| RSRK 50-877/2M | |
| RSRK 50-877/3M | |
| RSRK 50-877/5M | |
| RSRK 50-877/10M | |
| RSRK 50-877/20M | |

Pin Assignments

Face View 7/8"



1 = green2 = black 3 = white



1 = black2 = white 3 = red



1 = white























Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

RSRK 40-839/1M RSRK 50-877/0.3M RSRK 50-877/2M RSRK 50-877/5M RSRK 50-877/4M RSRK 40-839/18M RSRK 40-839/70M RSRK 40-839/7M RSRK 50-877/8M RSRK 40-839/2M RSRK 40-839/4M RSRK 50-877/80M RSRK 50-877/6M RSRK 50-877/0.6M RSRK 50-877/7M RSRK 40-839/40M RSRK 40-839/10M RSRK 40-839/80M RSRK 40-839/0.5M RSRK 50-877/1M RSRK 50-877/45M RSRK 50-877/70M RSRK 30-838/20M RSRK 50-877/25M RSRK 30-838/18M RSRK 50-877/0.5M RSRK 30-838/1M RSRK 30-838/3M RSRK 40-839/25M RSRK 50-877/12M RSRK 40-839/50M RSRK 50-877/20M RSRK 40-839/6M RSRK 30-838/8M RSRK 40-839/5M RSRK 40-839/23M RSRK 50-877/22M RSRK 50-877/60M RSRK 30-838/15M RSRK 50-877/13M RSRK 30-838/10M RSRK 30-838/25M RSRK 50-877/55M RSRK 30-838/12M RSRK 30-838/30M RSRK 50-877/40M RSRK 30-838/2M RSRK 50-877/35M RSRK 40-839/60M RSRK 40-839/3M RSRK 40-839/3M RSRK 40-839/3M RSRK 50-877/10M RSRK 50-877/10M RSRK 50-877/10M RSRK 50-877/10M RSRK 50-877/30M RSRK 50-877/30