

M12-Round-Plug Connector, Double-Ended Cordsets,


RST-RKT | RST-RKWT



3-, 4-, 5-, and 8-Poles


Actuator/sensor cordset, double-ended, M12, 3-, 4-, 5- and 8-poles, male straight to female straight connector with self-locking thread and molded cable.

RST-RKT



Actuator/sensor cordset, double-ended, M12, 3-, 4-, 5- and 8-poles, male straight to female 90° connector with self-locking thread and molded cable.

RST-RKWT





Pin Assignments

M12

3 poles





4 poles







8 poles



white brown green yellow grey pink blue red

Be Certain with Belden

M12-Round-Plug Connector, Double-Ended Cordsets

Technical Data

Environmental Degree of protection IP68 / Nema 6P -40°C (-40°F) / +90°C (+194°F) Operating temperature range Mechanical PUR, translucent gray Housing / Molded body Insert PUR orange Contact CuZn, gold-plated Coupling nut CuZn, nickel-plated 0-ring FKM **Electrical** Current rating 3-5 poles 4A 8 poles 1.5A 3-4 poles 250V Voltage rating

5-8 poles 30V

Cable Specifications

Cable No.	Outer Jacket	Conductor Size	Jacket Color	OD
659	PVC	22 AWG	Gray	.190" (4.82 mm)
646	PVC	22 AWG	Gray	.190" (4.82 mm)
647	PVC	22 AWG	Gray	.212" (5.38 mm)
661	PVC	24 AWG	Gray	.232" (5.89 mm)

Part Number	Pins	Standard Cable Lengths	Characteristics
RST 3-RKT 4-3-659/M	3	0.3M / 0.6M / 1.5M / 1M / 2M / 5M / 10M	
RST 4-RKT 4-646/M	4	0.3M / 0.6M / 1.5M / 1M / 2M / 3M / 5M / 6M / 10M / 12M	
RST 5-RKT 5-647/M	5	0.3M / 0.6M / 1M / 2M / 5M / 10M	
RST 8-RKT 8-661/M	8	0.3M / 0.6M / 1M / 2M / 5M / 10M	
RST 3-RKWT 4-3-659/M	3	0.3M / 0.6M / 1.5M / 1M / 2M / 5M / 10M	
RST 4-RKWT 4-646/M	4	0.3M / 0.5M / 0.6M / 1.5M / 1M / 2M / 5M / 10M	
RST 5-RKWT 5-647/M	5	0.3M / 0.6M / 1M / 2M / 5M / 10M	
RST 8-RKWT 8-661/M	8	0.3M / 0.6M / 1M / 2M / 5M / 10M	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

RST 8-RKWT 8-661/0.6M RST 4-RKWT 4-646/0.3M RST 3-RKWT 4-3-659/2M RST 8-RKWT 8-661/0.3M RST 5-RKWT 5-647/0.6M RST 3-RKWT 4-3-659/1M RST 5-RKWT 5-647/3M RST 3-RKT 4-3-659/2M RST 3-RKT 4-3-659/5M RST 8-659/1.5M RST 3-RKT 4-3-659/1M RST 4-RKT 4-646/3M RST 5-RKT 5-647/1.5M RST 3-RKWT 4-3-659/5M RST 8-RKT 8-661/2M RST 4-RKT 4-646/6M RST 5-RKT 5-647/1M RST 4-RKT 4-646/10M RST 4-RKWT 4-646/0.6M RST 8-RKKT 8-661/10M RST 4-RKWT 4-646/0.6M RST 3-RKWT 8-661/2M RST 4-RKWT 4-646/5M RST 4-RKWT 5-647/0.3M RST 5-RKWT 4-646/0.5M RST 8-RKWT 8-661/2M RST 3-RKWT 4-3-659/0.6M RST 8-RKWT 8-661/1M RST 5-RKWT 8-661/1M RST 5-RKWT 8-661/1M RST 3-RKWT 8-661/1M RST 8-RKWT 8-661/1M RST 8-RKWT 8-661/5M RST 4-RKKT 4-646/1M RST 5-RKWT 8-661/5M RST 4-RKWT 4-646/2M RST 8-RKWT 8-661/5M RST 4-RKWT 4-646/0.3M RST 3-RKT 4-3-659/0.3M RST 3-RKWT 8-661/10M RST 8-RKWT 8-661/15M RST 4-RKWT 4-646/6M RST 8-RKWT 8-661/1M RST 3-RKWT 4-3-659/0.3M RST 8-RKWT 8-661/10M RST 8-RKWT 8-661/10M