

M12-Round-Plug Connector, Single-Ended Cordsets, According to IEC 61076-2-101


RSTS



4-, 5-, and 8-Poles (Shielded)

Actuator/sensor cordset, single-ended, M12, 4-, 5-, and 8-poles, male straight connector with threaded joint and molded cable, shielding connecting to knurled screw.


RSTS




Pin Assignments

M12 - Male


4 poles



5 poles



8 poles





Be Certain with Belden

M12-Round-Plug Connector, Single-Ended Cordsets, According to IEC 61076-2-101
RSTS**Technical Data****Environmental**

Degree of protection	IP 67 / NEMA 6P
Operating temperature range	-25°C (-13°F) / +80°C (+176°F)

Mechanical



















Housing / Molded body	TPU
Insert	TPU
Contact	CuSn, pre-nickeled and 0.8 microns gold-plated
Coupling nut	CuZn, nickel-plated
Shield sleeve	CuZn, nickel-plated
O-ring	FKM

Electrical

Contact resistance	≤ 5 mΩ
Nominal current at 40°C	4–5 poles 4 A 8 poles 2 A
Nominal voltage	4 poles 240 V 5 poles 60 V 8 poles 30 V
Rated voltage	4 poles 250 V 5 poles 63 V 8 poles 36 V
Test voltage	4 poles 2.0 kV eff. / 60 s 5–8 poles 1.5 kV eff. / 60 s
Insulation resistance	> 10 ⁹ Ω
Pollution degree	3

Cable Specifications

Cable No.	Outer Jacket	Conductor Size	Jacket Color	OD
182	PVC, shielded	4 x 0.34 mm ²	Orange	.217" (5.5 mm)
183	PVC, shielded	5 x 0.34 mm ²	Orange	.236" (6.0 mm)
184	PVC, shielded	8 x 0.25 mm ²	Orange	.260" (6.6 mm)
288	PUR, halogen-free, shielded	4 x 0.34 mm ²	Black	.217" (5.5 mm)
298	PUR, halogen-free, shielded	5 x 0.34 mm ²	Black	.236" (6.0 mm)
299	PUR, halogen-free, shielded	8 x 0.25 mm ²	Black	.260" (6.6 mm)

Part Number	Pins	Outer Jacket	Standard Cable Lengths	Characteristics
RSTS 4-182/...M	4	PVC	2 M / 5 M / 10 M	  
RSTS 4-288/...M		PUR, halogen-free	2 M / 5 M / 10 M	  
RSTS 5-183/...M	5	PVC	2 M / 5 M / 10 M	  
RSTS 5-298/...M		PUR, halogen-free	2 M / 5 M / 10 M	  
RSTS 8-184/...M	8	PVC	2 M / 5 M / 10 M	  
RSTS 8-299/...M		PUR, halogen-free	2 M / 5 M / 10 M	  

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

[RSTS 5-298/15 M](#) [RSTS 5-183/3 M](#) [RSTS 5-298/5 M](#) [RSTS 5-183/10 M](#) [RSTS 5-298/10 M](#) [RSTS 5-183/2 M](#) [RSTS 8-299/2 M](#) [RSTS 5-183/1 M](#) [RSTS 8-184/15 M](#) [RSTS 8-299/5 M](#) [RSTS 4-288/2 M](#) [RSTS 5-183/5 M](#) [RSTS 5-183/15 M](#) [RSTS 8-184/10 M](#) [RSTS 8-299/15 M](#) [RSTS 4-288/10 M](#) [RSTS 8-299/10 M](#) [RSTS 5-298/2.5 M](#) [RSTS 4-288/5 M](#) [RSTS 8-299/25 M](#) [RSTS 5-298/2 M](#) [RSTS 5-183/9 M](#) [RSTS 4-182/5 M](#)