

AX104595 Modular Connectors - Cat5e Shielded KeyConnect Modular Jack



For more Information
please call

1-800-Belden1

**General Description:**

CAT 5e Shielded KeyConnect Modular Jack, Category 5e, RJ45

Usage (Overall)

Suitable Applications:	IBDN Shielded System 1200, TIA Screened Category 5e , ISO Class D, 1000BASE-T
Related Parts:	Compatible with Shielded KeyConnect Patch Panels 24-p , 48-p, See notes if using with Belden faceplates.

Physical Characteristics (Connectivity)**Dimensions**

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
1.000	0.675	1.570

Materials

Materials:

Description	Type	Material
Front Connection	RJ45	Phosphor Bronze with 50u inch Gold over Nickel Plating
Rear Connection	IDC	Phosphor Bronze with Tin Plating over Nickel
Connector Body	N/A	Metal

Wiring Scheme

Wiring Scheme:	T568A/B
-----------------------	---------

Weight

Weight:	0.048 lbs.
----------------	------------

Included Parts

Included Parts:	1 Termination Bar, 1 cable Tie
------------------------	--------------------------------

Packaging

Packaging:	Individually packaged in a plastic bag. Standard pack of 70 units.
-------------------	--

Mechanical Characteristics (Connectivity)

Footprint/Type:	KeyConnect
Plug / Jack Compatibility:	RJ45, RJ11

Termination Interface:

Termination	Connection	Durabilities
Front	Mated Connection	750 cycles
Rear	IDC Connection	20 terminations

Cable/Connector Retention:	15 lbs.
Connector/Hardware Retention:	20 lbs.
Plug/Connector Retention:	11.250 lbs.
Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C
Tool Compatibility:	Tool Less

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

Other Standards:	FCC Part 68, Subpart F, IEC 60603-7
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2011
MII Order #39 (China RoHS):	EUP 50

AX104595 Modular Connectors - Cat5e Shielded KeyConnect Modular Jack

Telecommunications Standards:	Category 5e - IIA 568.C.2, Category 5 - ISO/IEC 11801:2002 Ed.2
--------------------------------------	---

Third Party Performance Verification:	ETL - Verified Category 5e
--	----------------------------

Safety Listing:	Bi-national Standard Listed
------------------------	-----------------------------

Suitability

Suitability - Indoor:	Yes - Indoor
------------------------------	--------------

Transmission Characteristics (Connectivity)

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
-----------------------------	----------------------------------

Current Rating:	1.500 A
------------------------	---------

Insulation Resistance:	500 M-Ohm Minimum
-------------------------------	-------------------

Max. Contact Resistance:	20 m-Ohm
---------------------------------	----------

Termination Resistance:	2.5 m-Ohm
--------------------------------	-----------

Notes (Overall)

Notes: May not be compatible with all Belden faceplates. Please contact Belden Technical Support for compatibility verification.

Product Family**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX104595	1 EA	0.040 KG			Cat 5e Shielded Modular Jack

Revision Number: 1 Revision Date: 07-27-2017

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[AX104595](#)