

B9W231 Fiber - Interlocked Armor Distribution Cable - Riser



For more Information
please call

1-800-Belden1



General Description:

FiberExpress Distribution Aluminum Interlocked Armor Cable, 12-Fiber, OS2 OFCR, Tight Buffer, Indoor Rated with Yellow Jacket, Rugged construction that affords superior protection in adverse environments.

Physical Characteristics (Overall)

Product Family - Plenum:

Fiber Count	Type	OM1 MM 62.5/125 1 Gb	OM2 MM 50/125 1 Gb	OM3 MM 50/125 10 Gb 300m	OM4 MM 50/125 10 Gb 500m	OS2 - SM
6	Indoor	B9B240	B9A240	B9C240	B9E240	B9W240
6	Indoor/Outdoor	B9B240T	B9A240T	B9C240T	B9E240T	B9W240T
12	Indoor	B9B241	B9A241	B9C241	B9E241	B9W241
12	Indoor/Outdoor	B9B241T	B9A241T	B9C241T	B9E241T	B9W241T
24	Indoor	B9B243	B9A243	B9C243	B9E243	B9W243
24*	Indoor	B9B242	B9A242	B9C242	B9E242	B9W242
24*	Indoor/Outdoor	B9B242T	B9A242T	B9C242T	B9E242T	B9W242T
36	Indoor	B9B244	B9A244	B9C244	B9E244	B9W244
48	Indoor	B9B245	B9A245	B9C245	B9E245	B9W245
72	Indoor	B9B246	B9A246	B9C246	B9E246	B9W246
72	Indoor/Outdoor	B9B246T	B9A246T	B9C246T	B9E246T	B9W246T
96	Indoor	B9B247	B9A247	B9C247	B9E247	B9W247
144	Indoor	B9B248	B9A248	B9C248	B9E248	B9W248
*						

Product Family - Riser:

Fiber Count	Type	OM1 MM 62.5/125 1 Gb	OM2 MM 50/125 1 Gb	OM3 MM 50/125 10 Gb 300m	OM4 MM 50/125 10 Gb 500m	OS2 - SM
6	Indoor	B9B230	B9A230	B9C230	B9E230	B9W230
6	Indoor/Outdoor	B9B230T	B9A230T	B9C230T	B9E230T	B9W230T
12	Indoor	B9B231	B9A231	B9C231	B9E231	B9W231
12	Indoor/Outdoor	B9B231T	B9A231T	B9C231T	B9E231T	B9W231T
24	Indoor	B9B233	B9A233	B9C233	B9E233	B9W233
24*	Indoor	B9B232	B9A232	B9C232	B9E232	B9W232
24	Indoor/Outdoor	B9B232T	B9A232T	B9C232T	B9E232T	B9W232T
36	Indoor	B9B234	B9A234	B9C234	B9E234	B9W234
48	Indoor	B9B235	B9A235	B9C235	B9E235	B9W235
72	Indoor	B9B236	B9A236	B9C236	B9E236	B9W236
96	Indoor	B9B237	B9A237	B9C237	B9E237	B9W237
144	Indoor	B9B238	B9A238	B9C238	B9E238	B9W238
*						

Fiber Type: SM, (OS2)

Number of Fibers: 12

Core Diameter: 92.

Clad Diameter: 125

Primary Coating Diameter: 250

Buffer Tube Material: Thermoplastic

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Strength Member

Strength Member Material: Aramid Yarn

Armor

B9W231 Fiber - Interlocked Armor Distribution Cable - Riser

Armor Type: Interlocked

Armor Material: Aluminum

Overall Cable

Overall Nominal Diameter: 15.748 mm

Mechanical Characteristics (Overall)

Storage Temperature Range: -40°C To +70°C

Installation Temperature Range: 0°C To +60°C

Operating Temperature Range: -20°C To +70°C

Bulk Cable Weight: 223.230 Kg/Km

Min. Bend Radius/Minor Axis: 314.960 mm

Min. Bend Radius for Long Term Application: 236.220 mm

Max. Load for Installation: 1334.460 N

Max. Load for Long Term Application: 400.338 N

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: OFCR

CEC/C(UL) Specification: OFC

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 08/01/2008

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MIL Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1666 Riser

CSA Flame Test: FT4

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: No

Suitability - Aerial: No

Suitability - Burial: No

Sunlight Resistance: No

Plenum/Non-Plenum

Plenum (Y/N): No

Optical Characteristics (Overall)

Maximum Attenuation @ 1310nm: .8 dB/km

Maximum Attenuation @ 1550nm: .5 dB/km

Maximum Gigabit Ethernet Length @ 1300nm: 5000 meters

Fiber Coding MLT EMEA:

Fiber/Tube No.	Color
1	Blue
2	Orange
3	Green
4	Brown
5	Slate
6	White
7	Red
8	Black
9	Yellow
10	Violet

METRIC MEASUREMENT VERSION

B9W231 Fiber - Interlocked Armor Distribution Cable - Riser

11	Rose
12	Aqua

Related Documents:

[DOUBLE JACKETED INTERLOCKED ARMOR DISTRIBUTION CABLE.pdf](#) - Document PG 46 - DOUBLE JACKETED INTERLOCKED ARMOR DISTRIBUTION CABLE rev 8.pdf

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
B9W231	1 FT	0.192 LB	YELLOW		REPLACED BY F1SD012F9

Revision Number: 3 Revision Date: 08-05-2013

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[B9W231](#)