


Product: [MDVO RCA INSERT](#) 



MDVO RCA Faceplate Inserts

Product Description

MDVO RCA Faceplate Inserts. Available in several colors.

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	RCA Cable

Physical Characteristics (Overall)

Height:	0.63 m
Width:	0.63
Depth:	1.293
Front Connection:	Flush
Packaging:	10 units packaged in a plastic bag.
Weight:	0.034 lbs

Connectors

Materials

Material
Plastic - UL94V-0

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	MDVO
Connector/Hardware Retention:	20 lbs

Applicable Environmental and Other Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-07-01
MII Order #39 (China RoHS):	EUP 50

Flammability, LSOH, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Part Number

Related Parts:	Compatible with MDVO Patch Panel and Faceplate, RCA Cable Assembly
----------------	--

Variants

Item #	Color	UPC
--------	-------	-----

AX101824	Almond	611589003643
AX101828	Almond	611589003681
AX101832	Almond	611589003728
AX101836	Almond	611589003766
AX101826	Black	611589003667
AX101830	Black	611589003704
AX101834	Black	611589003742
AX101838	Black	611589003780
AX101823	Gray	611589003636
AX101827	Gray	611589003674
AX101831	Gray	611589003711
AX102601	Ivory	611589027724
AX102602	Ivory	611589027731
AX102603	Ivory	611589027748
AX101833	White	611589003735
AX101825	White	611589003650
AX101829	White	611589003698
AX101837	White	611589003773

Product Notes

Notes:	For proper installation refer to Installation Guide P0749391. Visit our web site at http://www.belden.com
--------	---

History

Update and Revision:	Revision Number: 0.170 Revision Date: 07-11-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[AX101829](#) [AX101825](#) [AX101838](#) [AX102603](#) [AX101837](#) [AX101828](#) [AX101824](#) [AX101834](#) [AX101827](#) [AX101830](#)
[AX101823](#) [AX101826](#) [AX102601](#) [AX101836](#) [AX101832](#) [AX101831](#) [AX102602](#) [AX101833](#)