

# Humidity/Temperature Pen

 **Pocket size meter**  
With Max/Min recording

## Features:

- Dual LCD for simultaneous display of Relative Humidity and Temperature
- Temperature is °C/°F switchable
- Built-in Humidity and Temperature sensors for convenient operation
- Pocket size for quick and reliable measurements at any location
- Max/Min memory functions for display of highest and lowest readings for both Temperature & Relative Humidity
- "Clear" function key to erase stored Max/Min readings to record new values
- Complete with pocket clip and one LR44 button battery



Specifications	% Relative Humidity	Temperature
Range	10 to 85%	14 to 122°F (-10 to 50°C)
Basic accuracy	± 5%	± 2°F/1°C
Resolution	1%RH	0.1°C or °F
Sensor Type	Resistive ceramic	Thermistor
Power	One LR44 button battery	
Dimensions	5.9 x 0.8 x 0.7" (150 x 20 x 18mm)	
Weight	0.7oz (20g)	

## Ordering Information:

44550 .....Humidity/Temperature Pen



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FLIR:](#)

[44550](#)