

EasyView™ Hygro-Thermometers

Relative Humidity, Temperature, Dew Point, and Wet Bulb measurements
With choice of Datalogger model

Features:

- Compact and rugged design features large display and bargraph
- Display any two parameters (Temperature and Humidity or Dew Point, or Wet Bulb) simultaneously
- Min/Max function stores & recalls highest and lowest readings
- Timer function displays the elapsed time (mins : secs and day : hour) to the minimum and maximum readings
- Programmable auto power off time frame
- Remote capacitance sensor with 39" (1m) coiled cable
- Switchable °C/°F temperature units
- Data Hold function freezes reading on display
- Auto power off to save battery life
- Low battery and overrange indication
- Complete with built-in stand, protective holster, probe and 6 AAA batteries

Model EA25 Additional Features:

- Datalogs up to 15,000 records plus automatic timer function
- Built-in RS-232 PC serial interface comes complete with Windows® 95/98/NT/2000/ME/XP compatible software and optically isolated RS-232 cable

Applications:

- Monitor Relative Humidity and Temperature in factories, clean rooms, offices, and greenhouses
- Produce reports of overnight or long term humidity and temperature fluctuations



Specifications:	Range	Resolution	Basic Accuracy
Humidity	10% to 95%	0.1%	±3% (30% to 95%) ±5% (10% to 30%)
Temperature	-4 to 140°F (-20 to 60°C)	0.1°	±1.8°F (±1°C)
Dimensions	5.9 x 2.8 x 1.4" (150 x 72 x 35mm)		
Weight	8.3oz. (235g)		

Ordering Information:

EA20EasyView Hygro-Thermometer
EA20-NIST.....EA20 with NIST Certificate
EA25EasyView Hygro-Thermometer Datalogger
EA25-NIST.....EA25 with NIST Certificate



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[EA20-NIST](#) [EA25-NIST](#) [EA25](#) [EA20](#)