

Industrial DMM/Clamp Meter Test Kit

CAT IV MultiMeter

And True RMS Clamp Meter with integrated AC Voltage Detector

Kit Includes:

- Model EX505 — Industrial grade, CAT IV 600V, 4000 count display, waterproof (IP67), drop-proof, rugged multimeter with True RMS functions; CE/UL listed
- Model MA620 — 600A True RMS 6000 count AC Clamp-on MultiMeter with built-in non-contact AC Voltage Detector, test leads and temperature probe; CE/ETL approved
- Set of double molded professional test leads
- Type K thermocouple bead probe and Type K to Banana Input Adaptor
- Includes a magnetic hanging strap for the multimeter
- Supplied in a soft carrying case that provides protection and organization for the meters whenever they are needed
- Dimensions: 9.8x8x2" (248x203x54mm);
Weight: 1.5lbs (680g)



Ordering Information:

MA620-K.....Industrial DMM/Clamp Meter Test Kit



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[MA620-K](#)