



TL841 Test Lead Kit

16-piece kit with multiple test lead tip configuration

- Test Lead Set with Straight Probes, 0.16" (4mm) long tips with removable category control tip covers; CAT III-1000V, 16A
- Alligator Clip Set, 5A, CAT III-300V
- TL743 Slim Reach Test Probe Set; CE
- Spade Lugs, 0.16" (4mm) opening, 30VAC/60VDC, 5A
- Test Leads, Right Angle and Straight End, CAT III-1000V, 16A
- Test Leads with Hook Tip, Pincer Tip, and Couplers
- Conveniently stored in a pouch case



TL833 Industrial Test Lead Set

11-piece kit with CAT III-1000V rating

- TL726 Double Molded Silicone Test Leads; CE
- TL740 Industrial Plunger Style Test Clips; CE
- TL741 Heavy Duty Plunger Style Hook Clip Set; CE
- TL708 Large Alligator Clip Set
- TL743 Slim Reach Test Probe Set; CE
- Type K Bead Probe with Banana Adaptor
- Conveniently stored in a pouch case



TL831 Master Electrical Test Lead Kit

12-piece kit industrial grade test leads

- TL726 Double Molded Silicone Test Leads; CE
- TL747 Electronic Sharp Test Probe Set
- TL741 Heavy Duty Plunger Style Hook Clip Set; CE
- TL742 Heavy Duty Plunger Style Pincer Grip Set
- TL740 Industrial Plunger Style Test Clips; CE
- TL709 Medium Alligator Clip Set; CE
- Conveniently stored in a pouch case



TL741 Heavy Duty Plunger Style Hook Clips

Spring loaded clip for gripping component lead or wire

- 1000V, 10A
- 0.08" (2mm) gripping diameter
- 5.5" (140mm) overall length
- CAT III-1000V/3A max; CAT III-1000V



TL742 Heavy Duty Plunger Style Pincer Grip Set

Insulated, flexible silicone shaft with good heat resistance

- 1000V, 4A
- 0.2" (5mm) jaw opening
- 6" (152mm) overall length
- CAT IV-600V; CAT III-1000V



TL743 Slim Reach Test Probe Set

Sharp point for piercing insulation

- 1000V, 16A
- 0.16" (4mm) tip and sharp 0.08" (2mm) diameter with removable category control tip covers
- 4.5" (115mm) overall length
- CAT IV-600V/10A max; CAT III-1000V
- Includes protective cap



TL744 Flat Blade Test Probe Set

Designed to fit outlet receptacles

- 1000V, 10A
- 0.16" (4mm) long x 0.1" (2.5mm) flat tip with removable category control tip covers; 4.9" (124mm) overall length
- CAT IV-600V; CAT III-1000V



TL747 Electronic Sharp Test Probe Set

CAT III-1000V; For use on high density components and boards and for piercing insulation

- 1000V, 6A max
- 0.16" (4mm) long tip with sharp 0.08" (2mm) diameter
- 4" (102mm) overall length



TL748 Spring Loaded Hook Tip Probes

Ideal for gripping a component lead or fine wire

- 1000V, 5A max
- 0.04" (1mm) gripping diameter
- 4.7" (120mm) overall length
- CAT IV-600V; CAT III-1000V



TL726 Double Molded Silicone Test Lead Set

Right angle and straight end flexible leads with shrouded banana plugs

- 63" (1.6m) long
- Protective collar and insulated sleeve
- 1000V, 10A
- CAT IV-600V; CAT III-1000V



Alligator Clip Sets

Toothed jaws for solid gripping of fine wires

- **TL708** Heavy Duty Large Alligator Clips — 1000V, 6A, CAT IV-600V; CAT III-1000V; 1" (26mm) jaw length; 1.6" (40mm) jaw opening; 4.2" (107mm) overall length
- **TL709** Medium Alligator Clips — 1000V, 10A, CAT III-1000V; 1.4" (37mm) jaw length; 0.8" (20mm) opening; 3.9" (98mm) overall length



TL740 Industrial Plunger Style Test Clip Set

Spring loaded clip with steel jaws

- 1000V, 10A
- 0.6" (15mm) jaw opening
- 6.1" (155mm) overall length
- CAT III-1000V

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[TL726](#) [TL741](#) [TL742](#) [TL748](#) [TL831](#) [TL833](#) [TL841](#)